




Connectors > PCB Connectors > Wire-to-Board Connectors > Wire-to-Board Connector Assemblies & Housings



Connector Product Type: **Connector Assembly**

Connector & Housing Type: **Receptacle**

Connector System: **Wire-to-Board**

Number of Positions: **3**

Centerline (Pitch): **2.54 mm [.1 in]**

Features

Product Type Features

Applied Pressure	Standard
Connector Product Type	Connector Assembly
Connector & Housing Type	Receptacle
Connector System	Wire-to-Board
Sealable	No
Connector & Contact Terminates To	Wire & Cable

Configuration Features

Number of Positions	3
Number of Rows	1

Electrical Characteristics

Termination Resistance	15 mΩ
Dielectric Withstanding Voltage (Max)	600 VAC
Insulation Resistance	5000 MΩ
Operating Voltage	267 V



Body Features

Primary Product Color	Black
-----------------------	-------

Contact Features

Contact Retention Within Housing	With
Contact Layout	Inline
Contact Type	Socket
PCB Contact Termination Area Plating Material Finish	Matte
PCB Contact Termination Area Plating Material	Tin
Contact Base Material	Phosphor Bronze
Contact Current Rating (Max)	3 A

Termination Features

Termination Method to Wire & Cable	Crimp, Insulation Displacement (IDC)
------------------------------------	--------------------------------------

Mechanical Attachment

Strain Relief	Without
Contact Retention Type Within Housing	Locking Lance
Panel Mount Feature	Without
PCB Mount Retention	Without
Mating Retention Type	Latch
Mating Retention	With
Connector Mounting Type	Cable Mount (Free-Hanging)

Housing Features

Housing Material	Thermoplastic
Centerline (Pitch)	2.54 mm[.1 in]

Dimensions

Connector Length	60.96 mm[2.4 in]
Connector Height	6.73 mm[.265 in]
Compatible Insulation Diameter Range	1.37 mm[.054 in]
Wire Size	.12 – .4 mm²

Usage Conditions

Operating Temperature Range	-65 – 105 °C[-85 – 221 °F]
-----------------------------	----------------------------

Operation/Application

Circuit Application	Signal
---------------------	--------



Industry Standards

Glow Wire Rating	Standard Part - Not Glow Wire
Compatible With Approved Standards Products	CSA LR7189, UL E28476
UL Flammability Rating	UL 94V-0

Packaging Features

Packaging Quantity	72
Packaging Method	Tube

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2023 (235) Candidate List Declared Against: JUNE 2023 (235) Does not contain REACH SVHC
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>


Compatible Parts



TE Part # 843477-1
TOOL, EXTRACTION RESET



TE Part # 5-103672-2
03 MTE HDR SRRA LATCH W/HLDWN



TE Part # 5-103634-2
03 MTE HDR SRRA LATCH.100CL LF



TE Part # 5-103639-2
03 MTE HDR SRST LATCH .100CL



TE Part # 5-103669-2
03 MTE HDR SRST LATCH W/HLDWN



TE Part # 58336-1
HEAD (IDC) MODU MTE W/O TL



TE Part # 5-147324-2
03 MTE HDR SRRA SMT.100CL



TE Part # 5-104450-2
03 MTE HDR SRST LATCH W/HLDWN



TE Part # 5-1375549-2
03 MTE VERT SMT HDR FULL LF-PB



TE Part # 58074-1
MTA 50/100/156 MANUAL TOOL FRAME



TE Part # 5-104915-2
03 MTE HDR SRST LATCH W/HLDWN

Also in the Series | AMPMODU MTE



Connector Caps & Covers(40)



Connector Contacts(32)



Connector Hardware(1)



Insertion & Extraction Tools(1)



PCB Headers & Receptacles(763)



Standard Rectangular Connectors(2)



Wire-to-Board Connector Assemblies & Housings(585)

Customers Also Bought



 TE Part #3-1879234-0 SMF5 8K2 5%	 TE Part #5-146257-8 16 MODII HDR DRST B/A .100CL L	 TE Part #5-104550-2 20 SYS50 SURFMNT DRST RCPT SN	 TE Part #60878-2 250 FASTON REC 22-18 AWG TPBR
 TE Part #5749231-1 Mini DIN, 6 pos, R/A, Shield	 TE Part #5-146281-6 06 MODII HDR SRST B/A .100CL	 TE Part #2-87456-2 26 MODIV HSG DR MRKD .100CL	 TE Part #5-104550-4 30 SYS50 SURFMNT DRST RCPT LF
 TE Part #9-6474612-2 FSN-22A-6	 TE Part #5-103956-4 4X5 MTE RCPT SR LATCH .100CL		

Documents

Product Drawings
8X3 MTE RCPT SR LATCH .100CL
English

CAD Files
3D PDF
3D
Customer View Model
ENG_CVM_CVM_5-103956-2_T.2d_dxf.zip
English
Customer View Model
ENG_CVM_CVM_5-103956-2_T.3d_igs.zip
English
Customer View Model
ENG_CVM_CVM_5-103956-2_T.3d_stp.zip
English
3D PDF
English



Customer View Model

[ENG_CVM_5-103956-2_P.2d_dxf.zip](#)

English

Customer View Model

[ENG_CVM_5-103956-2_P.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_5-103956-2_P.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

[AMP MODU MTE Section of Catalog 1307819](#)

English

[AMPMODU_INTERCONNECTION_SYSTEM_SECTION5_CONT](#)

English

[AMPMODU MTE INTERCONNECT SYSTEM](#)

English

Product Specifications

[Application Specification](#)

English