



Terminals & Splices > Automotive Terminals > TIMER, RECEPTACLE AND TAB



Terminal Type: **Receptacle**
Mating Tab Width: **1.6 mm [.063 in]**
Mating Tab Thickness: **.6 mm [.024 in]**
Terminal Transmits: **0 – 24 A (Low Power)**
Wire Size: **20 – 17 AWG**

[All TIMER, RECEPTACLE AND TAB \(330\)](#)

Features

Product Type Features

Receptacle Style	180°
Sealable	Yes
Primary Locking Feature	Locking Lance

Body Features

Terminal Seal Type	Single Wire Seal (SWS)
--------------------	------------------------

Contact Features

Contact Size	1.6mm
Contact Fabrication	Stamped & Formed
Wire Contact Termination Area Plating Material	Tin
Typical Current Rating	10 A
Crimp Type	F-Crimp
Terminal Type	Receptacle
Mating Tab Width	1.6 mm[.063 in]
Mating Tab Thickness	.6 mm[.024 in]
Interface Plating	Tin (Sn)

Termination Features



Termination Method to Wire & Cable	Crimp
Product Terminates To	Wire

Dimensions

Compatible Insulation Diameter Range	2.6 mm[.102 in]
Wire Size	.5 – 1 mm²
Wire Size Search	17 AWG, 18 AWG, 19 AWG, 20 AWG

Usage Conditions

Insulation Option	Uninsulated
Operating Temperature (Max)	80 °C, 85 °C, 90 °C, 100 °C, 105 °C, 110 °C, 120 °C, 125 °C, 130 °C[176 °F][185 °F][194 °F][212 °F][221 °F][230 °F][248 °F][257 °F][266 °F]
Operating Temperature Range	-40 – 130 °C[-40 – 266 °F]

Operation/Application

Compatible With Wire Base Material	Copper
------------------------------------	--------

Industry Standards

Compatible With Agency/Standards Products	IEC 664/664A (DIN VDE 0110)
---	-----------------------------

Packaging Features

Packaging Quantity	4000
Packaging Method	Reel

Other

Terminal Transmits	0 – 24 A (Low Power)
--------------------	----------------------

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2023 (235) Candidate List Declared Against: JUNE 2023 (235) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC



Free



Solder Process Capability

Not applicable for solder process capability


Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

 TE Part # 539960-1 AUSZ-WKZ,MICRO TIM.	 TE Part # 5-1579018-6 INSERTION TOOL	 TE Part # 2-1579018-7 EXTRACTION TOOL	 TE Part # 2-1897726-3 MT-2 SLD 10 PLUG ASSY GRY
 TE Part # 2151057-1 OCEAN_2.0_APPLICATOR-S-080F130O	 TE Part # 2151057-2 OCEAN_2.0_APPLICATOR-S-080F130O	 TE Part # 2305570-1 Strip Terminal Cutter-Side Feed-No Crimp	 TE Part # 5-2151057-1 OCEAN_2.0_APPLICATOR-S-080F130O
 TE Part # 5-2151057-2 OCEAN_2.0_APPLICATOR-S-080F130O	 TE Part # 7-2151057-1 OCEAN_2.0_APPLICATOR-S-080F130O	 TE Part # 7-2151057-2 OCEAN_2.0_APPLICATOR-S-080F130O	 TE Part # 7-2151057-7 OCEAN_2.0_SPARE_PART_KIT-080F130O





KIT


REPRESENTATION ONLY

TE Part # 7-2151935-7
OC-080F130O-
752_CRIMPTOOLINGKIT

Also in the Series | Micro Timer II




Automotive Connector Caps & Covers
(1)



Automotive Connector Locks &
Position Assurance(1)



Automotive Housings(32)



Automotive Terminals(29)



Connector Seals & Cavity Plugs(1)



Insertion & Extraction Tools(4)


Customers Also Bought



TE Part #969005-3
TIMER, RECEPTACLE AND TAB



TE Part #1564984-2
AMP MCP 2.8K, CONTACT, SWS



TE Part #5-968220-5
MQS0,63 Au rec CB unseal. 0,2-0,35




TE Part #2103177-1
PLUG ASSY, KEY A, TA,CPA, HVA280-
2PHI XE




TE Part #1563125-1
10POS, MIXED,TAB HSG



TE Part #1563126-1
2. LOCK,10 POS MALE HOUSING



TE Part #1-2236269-1
24POS, MIXED,REC HSG,
20GENYMCP,ASSY,CODA



TE Part #2035334-8
CONTACT, FEMALE0.64 ,20.35SQMM



Documents

Product Drawings

MT3 REC 1.6 Contact SRC Sn

English

CAD Files

Customer View Model

ENG_CVM_1241732-2_A2.3d_igs.zip

English

Customer View Model

ENG_CVM_1241732-2_A2.3d_stp.zip

English

Customer View Model

ENG_CVM_1241732-2_A2.2d_dxf.zip

English

3D PDF

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

Timer Interconnection System

English

Product Specifications

Application Specification

German

Application Specification

English