



Connectors > Contacts > Connector Contacts > D-Sub Conn Contacts: Socket, Phosphor Bronze, Signal, Size 20



Contact Type: **Socket**
Contact Mating Area Plating Material: **Gold**
Contact Retention Type Within Housing: **Snap-In**
Contact Size: **Size 20**
Wire Size: **28 – 24 AWG**

[All D-Sub Conn Contacts: Socket, Phosphor Bronze, Signal, Size 20 \(56\)](#)

Features

Contact Features

Mating Pin Diameter	1 mm
Contact Mating Area Plating Material Thickness	.76 µm
Contact Underplating Material	Nickel
PCB Contact Termination Area Plating Material	Tin
Contact Type	Socket
Contact Mating Area Plating Material	Gold
Contact Size	Size 20
Contact Base Material	Phosphor Bronze
Contact Current Rating (Max)	1.2 A

Termination Features

Termination Method to Wire & Cable	Crimp
Product Terminates To	Wire & Cable



Mechanical Attachment

Wire Insulation Support	With
Contact Retention Type Within Housing	Snap-In

Dimensions

Compatible Insulation Diameter Range	.76 – 1.02 mm[.03 – .04 in]
Wire Size	.08 – .22 mm²

Usage Conditions

Operating Temperature Range	-55 – 105 °C[-67 – 221 °F]
-----------------------------	----------------------------

Operation/Application

Circuit Application	Signal
---------------------	--------

Identification Marking

Contact Color Code	Red
--------------------	-----

Packaging Features

Packaging Quantity	1000
Packaging Method	Loose Piece

Product Compliance

For compliance documentation, visit the product page on [TE.com](#)>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2023 (235) Candidate List Declared Against: JUNE 2023 (235) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products



will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

TE Part # 91503-1
CCII AMPLIMITE 20 DF PIN SKT 28-20 ASSY

TE Part # 1579007-9
EXTRACTION TOOL

TE Part # 91285-1
INSERT/EXTRACT TOOL ASSEMBLY

Customers Also Bought

TE Part #1658612-4
09 POS HDF RCPT, MS, LEAD FREE

TE Part #167294-1
25P HDP20 PLUG ASSY

TE Part #1676264-2
RN 0805 249R 0.1% 10PPM 1KRL

TE Part #1393236-8
V23092-A1012-A302

TE Part #1-216791-0
AMP LATCH D/P ASSY

TE Part #2-2176089-0
RP 1J 0.166W 17K4 0.1% 25PPM 1K RL

TE Part #1623254-1
CRG0805 1% 56K

TE Part #336765-000
CWT-3807-W1

TE Part #5-2176264-9
RN 0805 4R75 0.1% 10PPM 1K RL

TE Part #2-1377172-8
SMP 0-0160075-0

Documents

Product Drawings



20DF COSI SOCKET

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_166292-1_AF.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_166292-1_AF.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_166292-1_AF.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

AMPLIMITE Subminiature D Connectors - Subminiature D Connectors for Cable Mounting

English

Product Specifications

Application Specification

English