

## H3-TCM2-43X-2+

10-4000MHz 50Ω 1:2 Balun


### APPLICATIONS

- differential modulator/demodulator and active mixers
- wideband push-pull amplifiers
- LTE, Cellular, PCS, UMTS, WiFi, WiMAX


### FEATURES

- Surface mount
- Impedance ratio: 1:2
- Available on tape and reel
- RoHS compliant and Pb free

### DIMENSIONS



### PCB LAYOUT



A	B	C	D	H	I	J
4.21	4.21	2.40	1.27	1.40	0.76	1.27
E	F	G	K			
1.11	0.90	2.00	4.83			


Unless otherwise stated dimensions are in mm

Tolerance: .xx ± 0.25, .xxx ± 0.05


### ELECTRICAL SPECIFICATIONS@25°C:

Parameters (P#: ENA PORT)	frequency band	Min.	Typ.	Max.	Unit
Port Impedance, Z0 (P1)			50		Ohm
Insertion Loss	10-4000MHz		1.3	3.0	dB
Amplitude Balance	10-4000MHz		0.5		dB
Phase Balance	10-4000MHz		7.0		Deg

### TEST CURVE




### FUNCTIONAL SCHEMATIC



### PIN CONFIGURATION

Pin No.	Function
1	Not used
2	Primary
3	Primary Dot
4	Secondary
6	Secondary Dot

### APPLICATION & TEST CIRCUIT



RF ports: P1/P2/P3

### ABSOLUTE MAXIMUM RATINGS

Parameter	Value
Input Power	200mW Max
DC Current	30mA Max
Operating Temperature Range	-40 to 85°C
Storage Temperature Range	-55 to 100°C

Tel: +86-28-85589664

E-mail: mr\_li@henglitaitech.com

Web: www.hltchips.com

Adress: No.198 Tianqin East Street, Gaoxin West District, Chengdu City