


355062KFT ACTIVE

CGS | CGS 3550

TE Internal #: 1-2176404-7

62K Ω , Thick Metal Film, Power Resistor, 1 %, 2 Termination, Taped & Reeled, 5 W, ± 100 ppm/ $^{\circ}$ C, Solder, Height .043 in [1.1 mm], CGS 3550[View on TE.com >](#)

Passive Components > Resistors > Surface Mount Resistors

Resistor Type: **Power Resistor**Number of Terminations: **2**Packaging Method: **Taped & Reeled**Passive Component Tolerance: **1 %**Element Type: **Thick Metal Film**

Features

Product Type Features

Resistor Type	Power Resistor
Element Type	Thick Metal Film

Configuration Features

Number of Resistors	1
---------------------	---

Electrical Characteristics

Operating Voltage	300 V
Passive Component Tolerance	1 %
Resistance Class	1k Ω – 1M Ω
Resistance Value	62K Ω
Power Rating	5 W

Termination Features

Number of Terminations	2
Surface Mount Resistor Termination Type	Solder

Dimensions

Product Height	1.1 mm[.043 in]
Product Length	11 mm[.433 in]
Product Width	5 mm[.197 in]

Usage Conditions

Temperature Coefficient	± 100 ppm/ $^{\circ}$ C
-------------------------	-----------------------------

Packaging Features

Packaging Method	Taped & Reeled
------------------	----------------

Product Compliance


For compliance documentation, visit the product page on [TE.com](https://www.te.com)>

EU RoHS Directive 2011/65/EU	Compliant with Exemptions
EU ELV Directive 2000/53/EC	Compliant with Exemptions
China RoHS 2 Directive MIIT Order No 32, 2016	Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2023 (235) Candidate List Declared Against: JUNE 2023 (235) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Reflow solder capable to 260 $^{\circ}$ C


Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



Also in the Series | CGS 3550



Surface Mount Resistors(254)

Customers Also Bought

TE Part #413985-3
PLUG ASSY,STR,SMBTE Part #0969750001
TMS-SCE-1K-3/32-2.0-9TE Part #1-5227079-6
COMM BNC PLUGTE Part #5103309-5
A/L LOW PRO HDR 20P VERT BLACKTE Part #1-534206-3
26 MODII VRT DR CE 100/115TE Part #534206-3
06 MODII VRT DR CE 100/115TE Part #2355443-1
RJ45 CAT5e PANEL MOUNT SOCKETTE Part #9-2176403-7
3550 10K 1%



Documents

Product Drawings

3550 62K 1%

English

CAD Files

3D PDF

3D

Customer View Model

[ENG_CVM_CVM_1-2176404-7_A.2d_dxf.zip](#)

English

Customer View Model

[ENG_CVM_CVM_1-2176404-7_A.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_1-2176404-7_A.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

[SMD HIGH POWER RESISTORS - TYPE 3550 SERIES](#)

English