

1-2308272-1  ACTIVE

Rail D-Sub Backshells

TE Internal #: 1-2308272-1

Cable Clamp Kit, Zinc, Shell Size 1, Shielded, Rail D-Sub Backshells

[View on TE.com >](#)



Connectors > Connector Accessories > Connector Strain Relief > Cable Clamp for Size 1-3 STD/1-4 QL Shell



Strain Relief Accessory Type: **Cable Clamp Kit**

Primary Product Material: **Zinc**

Compatible With Connector Shell Size: **1**

Shielded: **Yes**

Operating Temperature Range: **-40 – 90 °C [-40 – 194 °F]**

[All Cable Clamp for Size 1-3 STD/1-4 QL Shell \(8\)](#)

Features

Product Type Features

Strain Relief Accessory Type	Cable Clamp Kit
------------------------------	-----------------

Body Features

Cable Exit Angle	180°
------------------	------

Primary Product Material	Zinc
--------------------------	------

Housing Features

Compatible With Connector Shape	D-Shaped
---------------------------------	----------

Body Orientation	Straight
------------------	----------

Usage Conditions

Operating Temperature Range	-40 – 90 °C [-40 – 194 °F]
-----------------------------	----------------------------

Operation/Application

Compatible With Connector Shell Size	1
--------------------------------------	---

Shielded	Yes
----------	-----

Product Compliance

For compliance documentation, visit the product page on [TE.com](https://www.te.com)>

EU RoHS Directive 2011/65/EU	Compliant with Exemptions
EU ELV Directive 2000/53/EC	Not Yet Reviewed
China RoHS 2 Directive MIIT Order No 32, 2016	Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	<p>Current ECHA Candidate List: JUNE 2023 (235) Candidate List Declared Against: JUNE 2023 (235) SVHC > Threshold: Pb (3.5% in Component Part)</p> <p>Article Safe Usage Statements: Do not eat, drink or smoke when using this product. Wash thoroughly after handling. Recycle if possible and dispose of the article by following all applicable governmental regulations relevant to your geographic location.</p>
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not reviewed for solder process capability

Product Compliance Disclaimer


This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 1-2308346-1
FULL METAL HOODS SIZE 5

Also in the Series | Rail D-Sub Backshells



Customers Also Bought



Documents

Product Drawings

CABLE CLAMPS (CASE RAW)

English

CAD Files

3D PDF

3D

Customer View Model

[ENG_CVM_CVM_1-2308272-1_A.2d_dxf.zip](#)

English

Customer View Model

[ENG_CVM_CVM_1-2308272-1_A.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_1-2308272-1_A.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

Rail D-Sub Backshells Flyer

English