



Connectors > Contacts > Connector Contacts



Contact Type: **Socket**

Contact Mating Area Plating Material: **Gold**

Wire Contact Termination Area Plating Material: **Tin**

Operating Voltage: **600 VAC**

Contact Retention Within Housing: **Without**

Features

Product Type Features

Discrete Wire Type	Stranded
--------------------	----------

Electrical Characteristics

Operating Voltage	600 VAC
-------------------	---------

Contact Features

Mating Pin Diameter	2.18 mm[.086 in]
Contact Underplating Material Thickness	1.27 µm[50 µin]
Wire Contact Termination Area Plating Thickness	1.27 µm[50 µin]
Wire Contact Termination Area Plating Material Finish	Matte
Contact Mating Area Plating Material Thickness	.76 µm[30 µin]
Contact Orientation	Straight
Contact Underplating Material	Nickel
Contact Type	Socket
Contact Mating Area Plating Material	Gold
Wire Contact Termination Area Plating Material	Tin



Contact Retention Within Housing	Without
Contact Base Material	Phosphor Bronze
Contact Current Rating (Max)	7 A

Termination Features

Termination Method to Wire & Cable	Crimp
Product Terminates To	Wire & Cable

Mechanical Attachment

Wire Insulation Support	Without
-------------------------	---------

Dimensions

Compatible Insulation Diameter Range	3.3 – 5.08 mm[.13 – .2 in]
Wire Size	.5 – 2 mm²

Usage Conditions

Operating Temperature Range	-55 – 120 °C[-67 – 248 °F]
-----------------------------	----------------------------

Operation/Application

Circuit Application	Power
---------------------	-------

Industry Standards

Compatible With Agency/Standards Products	CSA, UL, VDE
---	--------------

Packaging Features

Packaging Quantity	2500
Packaging Method	Reel

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2023 (235) Candidate List Declared Against: JUNE 2023 (235) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free








Solder Process Capability

Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

 TE Part # 90547-1 ASSY PRO-CRIMPER UNIV M-N-L	 TE Part # 91506-1 CCII UNML UNML II PIN SKT 16-14 ASSY	 TE Part # 90547-2 PROCRIMPER DIE ASSY UNIV MNL	 TE Part # 770019-1 04P UMNLI IN-LNE PLUG HSG KIT
 TE Part # 770028-1 09P UMNLI IN-LINE CAP HSG KIT	 TE Part # 770026-1 04P UMNLI IN-LINE CAP HSG KIT	 TE Part # 770024-1 02P UMNLI IN-LINE CAP HSG KIT	 TE Part # 770029-1 12P UMNLI IN-LINE CAP HSG KIT
 TE Part # 770021-1 09P UMNLI IN-LINE PLUG HSG KIT	 TE Part # 770030-1 15P UMNLI IN-LINE CAP HSG KIT	 TE Part # 770018-1 03P UMNLI IN-LINE PLUG HSG KIT	 TE Part # 770027-1 06P UMNLI IN-LINE CAP HSG KIT





TE Part # 770025-1
03P UMNLI IN-LNE CAP HSG KIT



TE Part # 770017-1
02P UMNLI IN-LNE PLUG HSG KIT



TE Part # 770020-1
06P UMNLI IN-LNE PLUG HSG KIT




TE Part # 770023-1
15P UMNLI IN-LNE PLUG HSG KIT



TE Part # 770022-1
12P UMNLI IN-LNE PLUG HSG KIT



TE Part # 770016-1
05P UMNLI IN-LNE PLUG HSG KIT



TE Part # 91508-1
CCII UNML UNML II PIN SKT 20-18 ASSY

Also in the Series | Universal MATE-N-LOK



Circular Power Connectors(2)



Connector Caps & Covers(34)




Connector Contacts(209)




Connector Hardware(12)



Connector Seals & Cavity Plugs(27)



Connector Strain Relief(7)



Insertion & Extraction Tools(4)



Rectangular Connector Housings(1)



Rectangular Power Connectors(672)

Customers Also Bought



TE Part #1-5102162-2
A/L UNIV HDR 64P RA



TE Part #1879451-6
TE 600W 2R7 5% Bracket



TE Part #5406217-1
MJ ASSY,SG PSH W/RV PNL G TAB



TE Part #770020-1
06P UMNLI IN-LNE PLUG HSG KIT



TE Part #2151034-2
OCEAN_2.0_APPLICATOR-S-176O



TE Part #2-1445099-2
MICRO MNL HDR ASSY S/ROW LF



TE Part #1SNK516064R0000
ZS50-BK



TE Part #2151698-2
OCEAN_2.0_APPLICATOR-S-FA-176O



TE Part #1320928-4
STRIP GUIDE

Documents

Product Drawings

UMNL II SOK SN/AUNI/PHBZ

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_1-770006-0_S_c-1-770006-0-s.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_1-770006-0_S_c-1-770006-0-s.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_1-770006-0_S_c-1-770006-0-s.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages



SOFT_SHELL_PIN_SOCKET_CONNECTORS_STANDARD_DENSITY

English

Product Specifications

Application Specification

English