

178004-1

✓ ACTIVE

FASTIN-FASTON | FASTIN-FASTON 250

TE Internal #: 178004-1

Crimp Terminal Housings, Tab, Tab Housing, 4 Position, Straight, Natural, Nylon, Contact Mating Retention, Mating Alignment, FASTIN-FASTON 250

[View on TE.com >](#)

Terminals & Splices > Terminal Housings, Insulation Sleeves & Blocks > Crimp Terminal Housings



Terminal Type: **Tab**

Connector & Housing Type: **Tab Housing**

Number of Positions: **4**

Terminal Orientation: **Straight**

Primary Product Color: **Natural**

Features

Product Type Features

Sealable	No
Connector & Contact Terminates To	Wire & Cable
Connector & Housing Type	Tab Housing

Configuration Features

Number of Positions	4
---------------------	---

Body Features

Primary Product Color	Natural
-----------------------	---------

Contact Features

Terminal Type	Tab
Terminal Orientation	Straight
Contact Mating Retention	With

Mechanical Attachment

Mating Retention Type	Latch
-----------------------	-------

Mating Alignment

With

Connector Mounting Type

Cable Mount (Free-Hanging)

Housing Features

Housing Material

Nylon

Centerline (Pitch)

5.5 mm [.216 in]

Dimensions

Product Length

25 mm [.98 in]

Usage Conditions

Operating Temperature Range

-40 – 120 °C [-40 – 248 °F]

Packaging Features

Packaging Quantity

100

Product ComplianceFor compliance documentation, visit the product page on [TE.com](https://www.te.com)>

EU RoHS Directive 2011/65/EU

Compliant

EU ELV Directive 2000/53/EC

Compliant

China RoHS 2 Directive MIIT Order No 32, 2016

No Restricted Materials Above Threshold

EU REACH Regulation (EC) No. 1907/2006

Current ECHA Candidate List: JUNE 2023

(235)

Candidate List Declared Against: JAN 2022

(223)

Does not contain REACH SVHC

Halogen Content

Not Low Halogen - contains Br or Cl > 900 ppm.

Solder Process Capability

Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 176986-1
FF 250 PLUG HSG 1P NYLON NAT



TE Part # 178004-2
FF 250 PLUG HSG 4P NYLON BLACK



TE Part # 171260-2
FF 250 TAB HSG 12P NYLON BLACK



TE Part # 171260-3
FF 250 TAB HSG 12P NYLON BLACK




TE Part # 176992-1
250 DBL LOCK CAP IKEI 2P NAT




TE Part # 178001-1
250 DBL LOCK CAP IKEI 3P NAT


Also in the Series | FASTIN-FASTON 250




Crimp Terminal Housings(211)



Insertion & Extraction Tools(2)



PCB Terminals(2)



Quick Disconnects(254)

Customers Also Bought



TE Part #1717103-1
TH/025 CONNECTOR SYSTEM,
HOUSING



TE Part #1612288-1
SEALED 0.64/2.3II 60POS LEVER



TE Part #172320-2
POSITIVE LOCK 250 (6.3 MM)
HOUSING



TE Part #178448-2
EJ-2 DBL LOCK PLUG 2P ASSY B



Documents

Product Drawings

[FF 250 PLUG HSG 4P NYLON NAT](#)

English

CAD Files

[3D PDF](#)

3D

Customer View Model

[ENG_CVM_CVM_178004-1_C.2d_dxf.zip](#)

English

Customer View Model

[ENG_CVM_CVM_178004-1_C.3d_jgs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_178004-1_C.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

[White Paper: Nylon Discoloration](#)

English

Product Specifications

[Application Specification](#)

English