



Connectors > Contacts > Connector Contacts



Contact Type: **Pin**

Contact Mating Area Plating Material: **Tin**

Wire Contact Termination Area Plating Material: **Tin**

Operating Voltage: **250 VAC**

Contact Retention Within Housing: **With**

Features

Product Type Features

Discrete Wire Type	Stranded
--------------------	----------

Electrical Characteristics

Operating Voltage	250 VAC
-------------------	---------

Contact Features

Mating Square Post Dimension	.64 mm[.025 in]
Contact Underplating Material Thickness	1.27 µm[50 µin]
Wire Contact Termination Area Plating Thickness	2.54 µm[100 µin]
Wire Contact Termination Area Plating Material Finish	Bright
Contact Mating Area Plating Material Thickness	2.54 µm[100 µin]
Contact Mating Area Plating Material Finish	Bright
Contact Orientation	Straight
Contact Underplating Material	Nickel
Contact Type	Pin
Contact Mating Area Plating Material	Tin



Wire Contact Termination Area Plating Material	Tin
Contact Retention Within Housing	With
Contact Base Material	Brass
Contact Current Rating (Max)	5 A

Termination Features

Termination Method to Wire & Cable	Crimp
Product Terminates To	Wire & Cable

Mechanical Attachment

Wire Insulation Support	Without
Contact Retention Type Within Housing	Locking Lance

Dimensions

Compatible Insulation Diameter Range	.89 – 1.52 mm[.035 – .06 in]
Wire Size	.05 – .13 mm²

Usage Conditions

Operating Temperature Range	-40 – 105 °C[-40 – 221 °F]
-----------------------------	----------------------------

Operation/Application

Circuit Application	Power
---------------------	-------

Industry Standards

Compatible With Agency/Standards Products	VDE
---	-----

Packaging Features

Packaging Quantity	2000
Packaging Method	Bag

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2023 (235) Candidate List Declared Against: JUNE 2023 (235) Does not contain REACH SVHC



Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

TE Part # 91391-1
SDE PEW 12MICRO MNL HAND TOOL

TE Part # 91502-1
CCII MICRO MNL REC 30-26 ASSY

TE Part # 91391-2
SDE COMM MICRO MNL DIE SET

TE Part # 1586344-1
MICRO MATENLOK EXTRACTION TOOL

Also in the Series | Micro MATE-N-LOK

Connector Contacts(27)

Insertion & Extraction Tools(1)

Rectangular Power Connectors(469)

Customers Also Bought



TE Part #CV6257-000
SHF260-0113-2-9



TE Part #1-2834237-1
3P REC, IP67 VERTICAL T/H CONN,
NATURE



TE Part #1623141-1
CRG0805 1% 1M0



TE Part #1-794611-2
MICRO MNL RPT CNT,LS PC,30AU L



TE Part #794616-4
FREE HANG DBL ROW HSG 4 POS



TE Part #323030
SPLICE,SOLIS PARA HR 22-16



TE Part #2-2213766-7
AV19 SPL 5A POWER LED RED 24V



TE Part #2324697-4
PUSH GRIP CONNECTOR 4P



TE Part #EC0210-000
05811606



TE Part #7-1768801-4
LBC-13033

Documents

Product Drawings

PIN CONT 26-30 TIN PLATE L/P

English

CAD Files

Customer View Model

ENG_CVM_1-794613-0_B1.3d_igs.zip

English

Customer View Model

ENG_CVM_1-794613-0_B1.3d_stp.zip

English

Customer View Model

ENG_CVM_1-794613-0_B1.2d_dxf.zip

English

3D PDF

English

3D PDF

3D



Customer View Model

[ENG_CVM_CVM_1-794613-0_B.2d_dxf.zip](#)

English

Customer View Model

[ENG_CVM_CVM_1-794613-0_B.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_1-794613-0_B.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

[SOFT_SHELL_PIN_AND_SOCKET_CONNECTORS_CATALOG](#)

English

[MICRO MATE-N-LOK CONNECTOR SYSTEM](#)

English

Product Specifications

[Product Specification](#)

English