




SlimSeal | SlimSeal Standard Connectors

TE Internal #: 2-2106124-7

Plug & Socket Lighting Connectors, Wire-to-Wire, 1 Position, .1 mm [2.5 in] Centerline, Sealable, Wire & Cable, 400 VAC, SlimSeal Standard Connectors

[View on TE.com >](#)

Connectors > Lighting Connectors > Plug & Socket Lighting Connectors



Connector System: **Wire-to-Wire**
Number of Positions: 1
Centerline (Pitch): **.1 mm [2.5 in]**
Sealable: **Yes**
Connector & Contact Terminates To: **Wire & Cable**

Features

Product Type Features

Connector System	Wire-to-Wire
Sealable	Yes
Connector & Contact Terminates To	Wire & Cable

Configuration Features

Number of Positions	1
---------------------	---

Electrical Characteristics

Operating Voltage	300 VDC
-------------------	---------

Body Features

Primary Product Color	Black
-----------------------	-------

Contact Features

Contact Current Rating (Max)	3.5 A
------------------------------	-------

Housing Features

Centerline (Pitch)	.1 mm[2.5 in]
--------------------	---------------



Usage Conditions

Operating Temperature Range	-40 – 105 °C[-40 – 221 °F]
-----------------------------	----------------------------

Product Compliance

For compliance documentation, visit the product page on [TE.com](#)>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2023 (235) Candidate List Declared Against: JUNE 2023 (235) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

TE Part # 2106136-2
Assembly, Receptacle, 2-Position

TE Part # 2106136-3
Assembly, Receptacle, 3-Position

TE Part # 2106136-4
Assembly, Receptacle, 4-Position

TE Part # 2154852-1
SlimSeal Assy, Receptacle, 1-Position



TE Part # 2063957-2
SDE COMMERCIAL DIE

TE Part # 2063956-2
SDE COMMERCIAL DIE

TE Part # 2063956-1
SDE COMMERCIAL TOOL & DIE

TE Part # 2063957-1
SDE COMMERCIAL TOOL & DIE

Also in the Series | SlimSeal Standard Connectors

Ballast Connectors(4)

Plug & Socket Lighting Connectors(25)

Customers Also Bought

TE Part #1558676-1
T9GS1L24-5

TE Part #2106136-2
Assembly, Receptacle, 2-Position

TE Part #2106135-2
Assembly, Free Hanging Plug, SLC, 2 pos

TE Part #1-2106123-1
CONTACT,Recept, SLC, Tin Plated, On Stri

TE Part #1-2834018-2
2POS 5.0MM TEPS CONN.

TE Part #2154854-1
SlimSeal Assembly, Plug, 1 position

TE Part #2834085-1
2.54MM TOP ENTRY MSC 2P_GY

TE Part #1-1423673-6
W51-A151A1-7=CKTBKR,THERM, ROCK

TE Part #2361492-2
PCB Antenna,cable,MHF,698-2700MHz

TE Part #4-2176345-5
CRGCQ 1210 47K 1%



Documents

Product Drawings

Contact, Tab, Tin Plated, LP 22-16 AWG

English

CAD Files

Customer View Model

ENG_CVM_CVM_2-2106124-7_A1.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_2-2106124-7_A1.3d_stp.zip

English

Customer View Model

ENG_CVM_CVM_2-2106124-7_A1.2d_dxf.zip

English

3D PDF

3D

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

SLIMSEAL_SSL_CONNECOTS

English

Product Specifications

Application Specification

English