

APPLICABLE STANDARD									
RATING	OPERATING TEMPERATURE RANGE	-55 °C TO 85 °C	STORAGE TEMPERATURE RANGE	-40 °C TO 60 °C ⁽¹⁾					
	VOLTAGE	50 V AC	OPERATING HUMIDITY RANGE	RELATIVE HUMIDITY 95 % RH MAX. ⁽²⁾					
	STORAGE HUMIDITY RANGE	40 % TO 70 % ⁽¹⁾							
	CURRENT	REFER TO FX10-168pin DERATING CURVES FROM TEST REPORTS TR570E-20588							
SPECIFICATIONS									
ITEM		TEST METHOD	REQUIREMENTS	QT	AT				
CONSTRUCTION									
GENERAL EXAMINATION		VISUAL AND WITH MEASURING INSTRUMENT.	ACCORDING TO DRAWING.	x	x				
MARKING		CONFIRM VISUALLY.		x	x				
ELECTRIC CHARACTERISTICS									
CONTACT RESISTANCE [EIA-364-23]		100 mA and 20 mv OPEN CIRCUIT MAX.	60 mΩ MAX.	x	—				
INSULATION RESISTANCE [EIA-364-21]		100 V DC.	100 MΩ MIN.	x	—				
VOLTAGE PROOF [EIA-364-20]		150 V AC FOR 1 MINUTE.	NO FLASHOVER OR BREAKDOWN.	x	x				
MECHANICAL CHARACTERISTICS									
INSERTION AND WITHDRAWAL FORCES [EIA-364-13]		MEASURED BY APPLICABLE CONNECTORS.	INSERTION FORCE: 100.8 N MAX. WITHDRAWAL FORCE: 4.2 N MIN.	x	—				
MECHANICAL OPERATION [EIA-364-09]		50 TIMES INSERTIONS AND EXTRACTION.	① CONTACT RESISTANCE CHANGE: 10 mΩ OR LESS ② NO DAMAGE, CRACK AND LOOSENESS OF PARTS.	x	—				
RANDOM VIBRATION [EIA-364-28]		FREQUENCY: 20 TO 500 Hz POWER SPECTRAL DENSITY: 0.02 G ² /Hz OVERALL rms G: 3.1 Grms FOR 15 MINUTES IN THREE DIRECTIONS.	1) NO ELECTRICAL DISCONTINUITY OF 1μs OR MORE. 2) NO DAMAGE, CRACK OR LOOSENESS OF PARTS.	x	—				
SHOCK [EIA-364-27]		490 m/s ² , DURATION OF PULSE: 11 ms 3 EACH DIRECTION, 3 AXIS.		x	—				
ENVIRONMENTAL CHARACTERISTICS									
THERMAL SHOCK [EIA-364-32]		TEMPERATURE: -55 → 15 ~ 35 → 85 → 15 ~ 35 °C TIME: 30 → 5 → 30 → 5 min. UNDER 10 CYCLES	1) CONTACT RESISTANCE CHANGE: 10 mΩ OR LESS 2) NO DAMAGE, CRACK OR LOOSENESS OF PARTS.	x	—				
CYCLIC TEMPERATURE AND HUMIDITY [EIA-364-31]		@ 25 °C, 80% RH: 60 MIN DWELL TIME 30 MIN RAMP TIME @ 65 °C, 50% RH: 60 MIN DWELL TIME UNDER 24 CYCLES.		x	—				
DRY HEAT [EIA-364-17]		EXPOSED AT 105 °C, 1000 hr.		x	—				
MIXED FLOWING GAS [EIA-364-65]		EXPOSED AT 30 °C, 70% Cl ₂ : 10 ppb, NO ₂ : 200 ppb, H ₂ S : 10 ppb, SO ₂ : 100 ppb UNMATED 7 DAYS, MATED 7 DAYS.	1) CONTACT RESISTANCE CHANGE: 10 mΩ OR LESS 2) NO HEAVY CORROSION.	x	—				
REFLOW TEMPERATURE CONDITION [IPC / JEDEC J-STD-020C]		REFLOW PEAK TEMPERATURE : 260 °C AT CONNETOR SURFACE.	NO DEFORMATION OF CASE OF EXCESSIVE LOOSENESS OF THE TERMINAL.	x	—				
	COUNT	DESCRIPTION OF REVISIONS	DESIGNED	CHECKED	DATE				
REMARK ⁽¹⁾ THIS STORAGE INDICATES A LONG-TERM STORAGE STATE FOR THE UNUSED PRODUCT BEFORE THE BOARD MOUNTED. ⁽²⁾ NO DEW CONDENSATION IS PERMITTED.			APPROVED	HS. OKAWA	11. 03. 24				
			CHECKED	K.I. HIROKAWA	11. 03. 24				
			DESIGNED	DK. AIMOTO	11. 03. 23				
			DRAWN	DK. AIMOTO	11. 03. 23				
Note QT:Qualification Test AT:Assurance Test X:Applicable Test			DRAWING NO.	ELC4-330879-01					
	SPECIFICATION SHEET		PART NO.	FX10A-168P-SV2 (93)					
	HIROSE ELECTRIC CO., LTD.		CODE NO.	CL570-0302-1-93	1/1				