



Connectors > Contacts > Connector Contacts



Contact Type: **Tab**
Contact Mating Area Plating Material: **Silver**
Wire Contact Termination Area Plating Material: **Silver**
Wire Size: **5 – 6 mm²**

Features

Contact Features

Mating Tab Width	5.84 mm[.23 in]
Mating Tab Thickness	2.67 mm[.105 in]
Wire Contact Termination Area Plating Thickness	2.54 μm[100 μin]
Wire Contact Termination Area Plating Material Finish	Bright
Contact Mating Area Plating Material Thickness	2.54 μm[100 μin]
Contact Orientation	Right Angle
Contact Underplating Material	Copper
Contact Type	Tab
Contact Mating Area Plating Material	Silver
Wire Contact Termination Area Plating Material	Silver
Contact Base Material	Copper
Contact Current Rating (Max)	35 A

Termination Features

Termination Method to Wire & Cable	Crimp
Product Terminates To	Wire & Cable

Mechanical Attachment

Wire Insulation Support	With
-------------------------	------

Dimensions

Compatible Insulation Diameter Range	4.83 – 5.59 mm[.19 – .22 in]
--------------------------------------	------------------------------



Wire Size5 – 6 mm²

Usage Conditions

Operating Temperature Range-40 – 85 °C[-40 – 185 °F]

Operation/Application

Circuit ApplicationPower

Packaging Features

Packaging Quantity100

Packaging MethodBag

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EUCompliant

EU ELV Directive 2000/53/ECCompliant

China RoHS 2 Directive MIIT Order No 32, 2016No Restricted Materials Above Threshold

EU REACH Regulation (EC) No. 1907/2006Current ECHA Candidate List: JUNE 2023 (235)
Candidate List Declared Against: JUNE 2023 (235)
Does not contain REACH SVHC

Halogen ContentLow Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free

Solder Process CapabilityNot applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 206037-2
CPC PLUG ASSEMBLY SIZE 17-3



TE Part # 90384-1
HHHT TYPE XII MALE FEMALE 10
ASSY




TE Part # 69710-1
C-HEAD FRAME W/O DIES




TE Part # 7-1579008-6
UNLOCKING TOOL



TE Part # 66741-2
TYPE XII FEMALE CONT (L.P.)



TE Part # 356304-1
TOOL HOLDER ASSY, STRHT ACTION



TE Part # 90140-1
TYPE XII MALE FEMALE 10 DIE SET

Customers Also Bought




TE Part #206137-1
23-7 RECEPT STD SEX




TE Part #207486-1
SIZE 23-16 RECEPTACLE,CPC



TE Part #90384-1
HHHT TYPE XII MALE FEMALE 10
ASSY



TE Part #213982-1
R/A STRN RELIEF KIT,SZ 13,CPC



TE Part #176270-1
UNIV POWER PLUG HSG 1P F/H




TE Part #176281-1
UNIV POWER CAP HSG 1P F/H



TE Part #66260-4
MALE CONTACT ASSY. (L.P.)



TE Part #625235-000
D-128-0010



TE Part #91124-1
EXTRACTION TOOL



TE Part #2-1105051-2
HN.D-C-BU.AU.0,5

Documents



Product Drawings

MALE CONTACT ASSY. (L.P.)

English

CAD Files

Customer View Model

ENG_CVM_66259-4_Z.3d_igs.zip

English

Customer View Model

ENG_CVM_66259-4_Z.3d_stp.zip

English

Customer View Model

ENG_CVM_66259-4_Z.2d_dxf.zip

English

3D PDF

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

AMP Circular Connectors for Commercial Signal & Power Applications

English

Power Contacts

English

M_SERIES_PIN_AND_SOCKET_CONNECTORS

English

Product Specifications

Application Specification

English

Instruction Sheets

Instruction Sheet (U.S.)

English