




Connectors > Lighting Connectors > Poke-In Connectors > Poke-In Connector, BUCHANAN WireMate



Connector System: **Wire-to-Board**
Number of Positions: **2**
Centerline (Pitch): **4 mm**
Connector & Contact Terminates To: **Printed Circuit Board**
Connector Height: **4.48 mm [.176 in]**

[All Poke-In Connector, BUCHANAN WireMate \(51\)](#)

Features

Product Type Features

Product Line	Poke-In
Connector System	Wire-to-Board
Connector & Contact Terminates To	Printed Circuit Board

Configuration Features

Number of Positions	2
---------------------	---

Electrical Characteristics

Operating Voltage	400 VAC
-------------------	---------

Body Features

Primary Product Color	Natural
-----------------------	---------

Contact Features

PCB Contact Termination Area Plating Material Finish	Matte
Contact Underplating Material	Nickel



PCB Contact Termination Area Plating Material	Tin-Lead
Contact Current Rating (Max)	6 A

Termination Features

Termination Method to Printed Circuit Board	Surface Mount
---	---------------

Mechanical Attachment

Connector Mounting Type	Board Mount
-------------------------	-------------

Housing Features

Centerline (Pitch)	4 mm
--------------------	------

Dimensions

Compatible Insulation Diameter Range	2.1 mm
Connector Height	4.48 mm[.176 in]
Wire Size	18 – 22 AWG

Industry Standards

Compatible With Agency/Standards Products	UL
Compatible With Approved Standards Products	UL 1977, UL E28476
UL Flammability Rating	UL 94V-0

Packaging Features

Packaging Method	Tape & Reel
------------------	-------------

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2023 (235) Candidate List Declared Against: JUNE 2023 (235) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Reflow solder capable to 245°C

Product Compliance Disclaimer



This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

TE Part # 2834006-2

RELEASE POKE-IN
CONNECTOR_2POLES

TE Part # 2324697-3

PUSH GRIP CONNECTOR 3P

Customers Also Bought

TE Part #211870-2

SEALING CAP ASSY,SZ 13,CPC

TE Part #4-2176056-5

RLP73K 2B R68 5% 5K RL

TE Part #3-1478978-1

SMA R/A PCB SKT GB

TE Part #5-103634-2

03 MTE HDR SRRA LATCH.100CL LF

TE Part #1-794068-0

16P MINI UMNL HDR W/DH SN

TE Part #1734753-1

MINI USB, TYPE B, VERTICAL, T/H

TE Part #2-647123-3

03P MTA156 SHRD HDR ASSY SQ SN

TE Part #3-647123-2

12P MTA156 SHRD HDR ASSY SQ SN

Documents

- CAD Files
- 3D PDF
- 3D
- Customer View Model
- ENG_CVM_CVM_7-2834006-2_B.2d_dxf.zip



English

Customer View Model

[ENG_CVM_CVM_7-2834006-2_B.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_7-2834006-2_B.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

[Modular Releasable Poke-in datasheet](#)

English

[BUCHANAN WireMate Connectors Brochure](#)

[BUCHANAN WireMate Connectors Brochure](#)

English

[Modular Releasable Poke-in datasheet \(Chinese\)](#)

Product Specifications

[Application Specification](#)

English