



SPLICE

TE Internal #: 61769-1  
Splices, Thru Splice / Pigtail Splice, Serrated, 1200 – 2600 CMA  
Wire Size, Brass, 2 Serration, Length .12 in [3.05 mm], Reel, Open,  
SPLICE  
[View on TE.com >](#)

Terminals & Splices > Splices



Sealable: No  
Splice Features: Serrated  
Wire Size: 1200 – 2600 CMA  
Contact Base Material: Brass  
Splice Type: Pigtail Splice, Thru Splice

Features

Product Type Features

Sealable	No
Splice Type	Pigtail Splice, Thru Splice
Compatible With Discrete Wire Type	Solid, Stranded
Wire Insulation Support Retention Type	Non-Insulation Support

Configuration Features

Number of Serrations	2
Compatible With Wire & Cable Type	Discrete Wire

Body Features

Product Weight	.109 g
Splice Features	Serrated

Contact Features

Contact Base Material	Brass
Barrel Type	Open



Mechanical Attachment

Wire Insulation Support	Without
-------------------------	---------

Dimensions

Wire Size	1200 – 2600 CMA
Terminal Material Thickness	.51 mm[.02 in]
Product Length	3.05 mm[.12 in]

Usage Conditions

Insulation Option	Uninsulated
Operating Temperature Range	-40 – 110 °C[-40 – 230 °F]

Operation/Application

Compatible With Wire Base Material	Copper
------------------------------------	--------

Industry Standards

Government Qualified Splice	No
-----------------------------	----

Packaging Features

Packaging Quantity	25000
Packaging Method	Reel

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2023 (235) Candidate List Declared Against: JUNE 2023 (235) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability








Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent





chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>


Compatible Parts

 <p>TE Part # 62759-1 SPLICE 400-1300 .016 BR</p>	 <p>TE Part # 7-2266236-7 OCEAN_2.0_SPARE_PART_KIT-090F</p>	 <p>TE Part # 2266236-1 OCEAN_2.0_Applicator-S-090F</p>	 <p>TE Part # 2266236-2 OCEAN_2.0_Applicator-S-090FA</p>
 <p>TE Part # 2305570-1 Strip Terminal Cutter-Side Feed-No Crimp</p>	 <p>TE Part # 7-2266236-1 OCEAN_2.0_Applicator-S-090F</p>	 <p>TE Part # 7-2266236-2 OCEAN_2.0_Applicator-S-090FA</p>	

Also in the Series | SPLICE

 <p>Crimp Wire Pins, Tabs &amp; Ferrules(1)</p>	 <p>Splices(64)</p>
--	---

Customers Also Bought



TE Part #61399-1  
312 FASTON REC 16-12 AWG TPBR



TE Part #521411-1  
ULTRA-POD 250 ASY REC 22-18 AWG BR




TE Part #485043-1  
SPLICE 4000-9000 .020 BR



TE Part #63130-2  
SPLICE REC. 1500-5000 .020 BR



TE Part #61795-3  
RING 18-14 AWG TPBR




TE Part #63435-1  
250 FASTON REC 14-10 AWG SPBR



TE Part #1-2232893-1  
11P MONOPLUG 2.5



TE Part #520988-1  
ULTRA-POD 250 ASSY REC 22-18 AWG BR



TE Part #2-176498-6  
187 HSG. PL MKII REC. 15mm 2P BLUE



TE Part #1-176282-5  
AMP UNIVERSAL POWER CAP 2P GREEN

Documents

Product Drawings

SPLICE 1200-2600 .020 BR

English

CAD Files

3D PDF

3D

Customer View Model

ENG\_CVM\_CVM\_61769-1\_T\_c-61769-1-t.2d\_dxf.zip

English

Customer View Model

ENG\_CVM\_CVM\_61769-1\_T\_c-61769-1-t.3d\_igs.zip

English

Customer View Model

ENG\_CVM\_CVM\_61769-1\_T\_c-61769-1-t.3d\_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications



Application Specification

English