

## H3-ETC1-1T-2TR

0.1-200MHz, 50Ω , 1:1 Balun


### APPLICATIONS

- Ideally suited for high volume cellular and wireless applications.

### FEATURES

- Surface mount
- Impedance ratio: 1:1
- Available on tape and reel
- RoHS compliant and Pb free
- 260°C reflow compatible
- CT on Secondary

### DIMENSIONS




A	B	C
3.81	3.81	2.73
D		
1.27		

Unless otherwise stated dimensions are in mm


Tolerance: .xx ± 0.25, .xxx ± 0.05

### Land Pattern



E	F	G
4.83	3.30	1.40
H	I	
0.76	1.27	

### FUNCTIONAL SCHEMATIC




### PIN CONFIGURATION

Pin No.	Function
1	Secondary
2	Secondary CT
3	Secondary Dot
4	Primary Dot
5	Primary


### ELECTRICAL SPECIFICATIONS@25°C:

Parameters (P#: ENA PORT)	frequency band	Min.	Typ.	Max.	Unit
Port Impedance, Z0 (P1 / P2 / P3)			50/25/25		Ohm
Insertion Loss	0.1-200MHz		0.5	1.5	dB
Amplitude Balance	0.1-200MHz		0.2	±0.5	dB
Phase Balance	0.1-200MHz		1.0	±5	Deg

### TEST CURVE



### APPLICATION & TEST CIRCUIT



### ABSOLUTE MAXIMUM RATINGS

Parameter	Value
Input Power	250mW MAX
DC Current	30mA MAX
Operating Temperature Range	-40 to 85°C