




MTA 156

TE Internal #: 3-641217-2
Rectangular Power Connectors, Connector Assembly, Receptacle,
Wire-to-Board, 2 Position, 3.96 mm [.156 in] Centerline, Wire &
Cable, UL 94V-2, MTA 156

[View on TE.com >](#)

Connectors > Power Connectors > Rectangular Power > Rectangular Power Connectors



Rectangular Power Connector Type: **Connector Assembly**
Connector & Housing Type: **Receptacle**
Connector System: **Wire-to-Board**
Number of Positions: **2**
Centerline (Pitch): **3.96 mm [.156 in]**

Features

Product Type Features

Compatible With Discrete Wire Type	Stranded
Rectangular Power Connector Type	Connector Assembly
Connector & Housing Type	Receptacle
Connector System	Wire-to-Board
Sealable	No
Connector & Contact Terminates To	Wire & Cable

Configuration Features

Number of Positions	2
Number of Power Positions	2
Number of Rows	1

Electrical Characteristics

Operating Voltage	600 VAC
-------------------	---------

Body Features

Cable Exit Angle	90°
------------------	-----



Connector Profile	Standard
Contact Features	
Contact Layout	Inline
Contact Underplating Material Thickness	1.27 – 1.77 µm[1.27 – 1.77 µin]
Wire Contact Termination Area Plating Thickness	2.03 – 5.08 µm[80 – 200 µin]
Contact Mating Area Plating Material	Gold, Gold Flash over Palladium Nickel
Contact Underplating Material	Nickel
Contact Base Material	Copper Alloy
Contact Current Rating (Max)	7 A
Contact Retention Within Housing	With
Contact Type	Receptacle
Wire Contact Termination Area Plating Material	Tin
Contact Mating Area Plating Material Thickness	.076 µm[3 µin]
Termination Features	
Termination Method to Wire & Cable	Insulation Displacement (IDC)
Mechanical Attachment	
Strain Relief	With
Mating Retention	With
Mating Alignment	Without
Contact Retention Type Within Housing	Locking Lance
PCB Mount Alignment	Without
Panel Mount Feature	Without
PCB Mount Retention	Without
Mating Retention Type	Locking Ramp
Connector Mounting Type	Cable Mount (Free-Hanging)
Housing Features	
Wire & Cable IDC Installation Type	Closed End
Centerline (Pitch)	3.96 mm [.156 in]
Housing Color	Orange
Housing Material	Nylon
Dimensions	
Connector Height	9.02 mm [.355 in]



Product Length	7.92 mm[.312 in]
Compatible Insulation Diameter Range	2.41 mm[.095 in]
Wire Size	.8 – .9 mm ²

Usage Conditions

Operating Temperature Range	-55 – 105 °C[-67 – 221 °F]
-----------------------------	----------------------------

Operation/Application

Circuit Application	Power & Signal
---------------------	----------------

Industry Standards

CSA Rating	Certified, LR 7189
UL Rating	Recognized
Compatible With Agency/Standards Products	CSA, UL
Compatible With Approved Standards Products	UL E28476
UL Flammability Rating	UL 94V-2
Glow Wire Rating	Standard Part - Not Glow Wire

Packaging Features

Packaging Quantity	500
Packaging Method	Bag

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2023 (235) Candidate List Declared Against: JUNE 2023 (235) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability








Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as



EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

 TE Part # 58247-1 MTA 156 CRIMP HEAD REPAIR DISCRETE	 TE Part # 640643-2 02P MTA156 COVER F/T	 TE Part # 3-641208-2 02P MTA156 HDR ASSY FL ST LF	 TE Part # 643067-2 02P MTA156 MOLDED COVER
 TE Part # 640551-2 02P MTA156 COVER	 TE Part # 3-641210-2 02P MTA156 HDR FLRA FB 30AU LF	 TE Part # 643071-2 02P MTA156 FD-THRU COVER	 TE Part # 58074-1 MTA 50/100/156 MANUAL TOOL FRAME
 TE Part # 59804-1 MAINTENANCE TOOL	 TE Part # 3-641209-2 02P MTA156 HDR ASSY FL ST LF	 TE Part # 3-644759-2 02P MTA156 HDR ASSY STR LF	 TE Part # 58247-3 MTA 156 CRIMP HEAD PRODUCTION RBBN CABLE
 TE Part # 3-644631-2 02P MTA156 HDR ASSY STR LF	 TE Part # 641533-1 02P MTA156 CONN HSG,END CAP	 TE Part # 3-641202-2 02P MTA156 HDR ASSY PL 30AU LF	 TE Part # 3-644633-2 02P MTA156 HDR ASSY R/A LF



TE Part # 3-644760-2
02P MTA156 HDR ASSY FL ST LF

TE Part # 3-644761-2
02P MTA156 HDR ASSY R/A F/L LF

TE Part # 3-644807-2
02P MTA156 PSTD CONN 18AWG LF

TE Part # 3-644809-2
02P MTA156 PSTD CONN 22AWG LF

Also in the Series | MTA 156

Connector Caps & Covers(89)

Connector Contacts(4)

Connector Hardware(2)

Insertion & Extraction Tools(1)

PCB Headers & Receptacles(314)

Rectangular Power Connectors(691)

Standard Rectangular Connectors(336)

Customers Also Bought

TE Part #3-641217-8
08P MTA156 CONN ASSY 18AWG ORA

TE Part #3-641119-5
05P MTA156 HDR ASSY FL/ST LF

TE Part #1445715-2
75A HSG SUBASY BLACK

TE Part #1546310-6
6P .563" DR BARRIER STRIP

TE Part #3-641150-5
05P MTA156 ASSY 22AWG RED LF

TE Part #1-1419108-7
RT424024F

TE Part #204763-E
SMCB 26 F AB VV 7-23 CL * H007 137 E002

TE Part #244628-E
SMCIDC 12 KV AB VV 7-01 CL * H007 717 PO



Documents

Product Drawings

02P MTA156 CONN ASSY 18AWG ORA

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_3-641217-2_W.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_3-641217-2_W.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_3-641217-2_W.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications

Application Specification

Japanese

Application Specification

English

MTA 156 Ribbon Cable Connector Assemblies (English And Spanish)

English

MTA 156 Ribbon Cable Connector Assemblies (English And Spanish)

Japanese

Agency Approvals

Agency Approval Document

English