


62131-6 ✓ ACTIVE

TE Internal #: 62131-6

TE Internal Description: .090 CLUSTER REC.

[View on TE.com >](#)



Product Compliance

[For compliance documentation, visit the product page on TE.com >](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2023 (235) Candidate List Declared Against: JUNE 2023 (235) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 2150436-2
OCEAN_2.0_APPLICATOR-E-110F140F



TE Part # 235280-6
CLUSTER BLOCK HSG .090 DIA



TE Part # 7-2150436-7
OCEAN_2.0_SPARE_PART_KIT-110F140F



TE Part # 141101-2
RECEPT CLUSTER



TE Part # 62131-8
CLSTR PIN RCPT


Customers Also Bought




TE Part #61188-1
250 FASTON FLAG REC 16-12 AWG
TPBZ



TE Part #360052-1
125 DIA CLSTR BLK



TE Part #360051-1
CLUSTER BLOCK




TE Part #880631-5
CLUSTER BLOCK HSG .090 DIA



TE Part #881257-3
MAG-MATE TERMINAL



TE Part #735220-2
250 FASTON REC 18-14 AWG TPBR



TE Part #1380145-1
CLUSTER BLOCK HSG .090 DIA.



TE Part #880688-2
FF 250 TERMINAL 0.5-1.0MM2 0.39
X13.2TPBR



TE Part #1599105-1
RECEPTACLE CLUSTER PIN .090dia

Documents

Product Drawings**.090 CLUSTER REC.**

English

CAD Files**3D PDF**

3D

Customer View Model

[ENG_CVM_CVM_62131-6_AV.2d_dxf.zip](#)

English

Customer View Model

[ENG_CVM_CVM_62131-6_AV.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_62131-6_AV.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.**Datasheets & Catalog Pages****Magnet Wire Terminals & Splices**

English

Product Specifications**Engineering Report**

English

Agency Approvals**Agency Approval Document**

English