




Connectors > Terminal Blocks & Strips > PCB Terminal Blocks



Terminal Block Connector Type: **Header**

Connector System: **Wire-to-Board**

Number of Positions: **10**

Centerline (Pitch): **3.5 mm [.138 in]**

Number of Rows: **1**

Features

Product Type Features

Header Type	Fully Shrouded
Terminal Block Connector Type	Header
Connector System	Wire-to-Board
Connector & Contact Terminates To	Printed Circuit Board

Configuration Features

Number of Positions	10
Number of Rows	1

Electrical Characteristics

Operating Voltage	300 VAC
-------------------	---------

Body Features

Primary Product Color	Green
Product Orientation	Vertical

Contact Features

--	--



Contact Mating Area Plating Material	Tin
Contact Base Material	Phosphor Bronze
Contact Current Rating (Max)	11 A

Termination Features

Termination Post & Tail Length	3.4 mm[.134 in]
Termination Method to Printed Circuit Board	Through Hole - Solder

Mechanical Attachment

Connector Mounting Type	Board Mount
-------------------------	-------------

Housing Features

Housing Material	PA 66
Centerline (Pitch)	3.5 mm[.138 in]

Dimensions

Wire Size	.05 – 2 mm²
-----------	-------------

Usage Conditions

Operating Temperature Range	-40 – 105 °C[-40 – 221 °F]
-----------------------------	----------------------------

Operation/Application

Circuit Application	Power & Signal
---------------------	----------------

Packaging Features

Packaging Quantity	100
--------------------	-----

Product Compliance

For compliance documentation, visit the product page on [TE.com](#)>


EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2023 (235) Candidate List Declared Against: JUNE 2023 (235) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Wave solder capable to 240°C




Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>


Compatible Parts




TE Part # 1-284506-0
10 POS TERMINAL BLOCK PLUG STAC 3,




TE Part # 1-1986371-0
Str Plug, 3.5mm, Green, LH, 10




TE Part # 1-1776130-0
10P TERMINAL BLOCK HDR, HIGH TEMP




TE Part # 1-1986370-0
Str Plug, 3.5mm, Green, RH, 10



TE Part # 1-284514-9
19P TERMINAL BLOCK HDR DIR POL




TE Part # 1-796694-0
10 POS TERMINAL BLOCK HDR DIR. POL




TE Part # 2-796694-0
20 POS TERMINAL BLOCK HDR DIR. POL

Customers Also Bought




TE Part #5102153-5
A/L UNIV HDR 24P VERT



TE Part #284506-2
2 POS TERMINAL BLOCK PLUG STACK 3,



TE Part #284514-2
2 POS TERMINAL BLOCK HDR DIR. POL.



TE Part #1761606-3
IDC LOW PRO HDR 10P VERT LG LAT
BLK



TE Part #284506-3
3 POS TERMI-BLOK PLUG STACK 3,

TE Part #284514-3
3 POS TERMI-BLOK HDR DIR. POL.

TE Part #1986671-1
PLZN.KEY,TERMI-BLOK PLUG

TE Part #284514-4
4 POS TERMI-BLOK HDR DIR. POL.

TE Part #1-284506-2
12 POS TERMI-BLOK PLUG STAC 3,

Documents

CAD Files

Customer View Model

[ENG_CVM_1-284514-0_C2.2d_dxf.zip](#)

English

3D PDF

English

Customer View Model

[ENG_CVM_1-284514-0_C2.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_1-284514-0_C2.3d_stp.zip](#)

English

3D PDF

3D

Customer View Model

[ENG_CVM_CVM_1-284514-0_C.2d_dxf.zip](#)

English

Customer View Model

[ENG_CVM_CVM_1-284514-0_C.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_1-284514-0_C.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

[Eurostyle Terminal Blocks Focus Product Stock List](#)



English

[BUCHANAN TERMINAL BLOCKS CATALOG - EUROSTYLE TERMINAL BLOCKS](#)

English

[1-1773458-1_EURO_STYLE_TERMINAL_BLOCKS_QRG](#)

English

[Product Specifications](#)

[Application Specification](#)

English