




Terminals & Splices > Automotive Terminals



Terminal Type: **Receptacle**
Mating Tab Width: **2.8 mm** [.11 in]
Mating Tab Thickness: **.8 mm** [.031 in]
Wire Size: **.5 – 1 mm²**

Features

Product Type Features

Sealable	No
Primary Locking Feature	Locking Lance

Contact Features

Contact Size	2.8mm
Contact Fabrication	Stamped & Formed
Crimp Type	F-Crimp
Terminal Type	Receptacle
Mating Tab Width	2.8 mm[.11 in]
Mating Tab Thickness	.8 mm[.031 in]
Interface Plating	Tin (Sn)

Termination Features

Termination Method to Wire & Cable	Crimp
Product Terminates To	Wire & Cable

Dimensions

Wire Size	.5 – 1 mm²
-----------	------------

Usage Conditions

Insulation Option	Uninsulated
Operating Temperature (Max)	130 °C[266 °F]
Operating Temperature Range	-40 – 130 °C[-40 – 266 °F]



Packaging Features

Packaging Quantity	1000
Packaging Method	Box

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2023 (235) Candidate List Declared Against: JUNE 2023 (235) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

REPRESENTATION ONLY. DIE SET MAY VARY. TE

TE Part # 2390881-1
SDE F JR PWR TMR 0.5-1.0mm2 ASSY

TE Part # 2390881-2
SDE F JR PWR TMR 0.5-1.0mm2 DIE SET

REPRESENTATION ONLY. DIE SET MAY VARY. TE

TE Part # 2392900-1
SDE F JR/STD TIMER 0.5-1.0mm2 ASSY

TE Part # 2392900-2
SDE F JR/STD TIMER 0.5-1.0mm2 DIE SET


Customers Also Bought



TE Part #178327-5
DYNAMIC D/ROW HDR 16P V ASSY



TE Part #1-967623-6
Timer Connector Housing



TE Part #1318853-2
025 CAP HSG ASSY 24P



TE Part #2141576-2
32POS NANO MQS TL PLUG HOUSING, CODE B



TE Part #927777-3
JUNIOR POWER TIMER CONTACT



TE Part #936863-1
FAMILY SEAL FOR HYB 42P CAP



TE Part #2229745-1
HVA280 HEADER ASSY, KEY A, ORANGE



TE Part #BSA880N0086055A000
917 PLUG, SPEEDTEC



TE Part #K1070514
Schlagschalter (Hauptantr HK) 06-63-420

Documents

Product Drawings

JPT REC 2.8 Contact SRC Sn (LP)

English

CAD Files

Customer View Model

ENG_CVM_927779-3_A9.3d_igs.zip

English

Customer View Model

ENG_CVM_927779-3_A9.3d_stp.zip

English

Customer View Model

ENG_CVM_927779-3_A9.2d_dxf.zip

English

3D PDF

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications



Application Specification

English