

SPECIFICATION

Part No.	:	OMB.915.B03F21		
Description	÷	Barracuda - 915MHz 3dBi ISM Band Indoor/Outdoor Omnidirectional Antenna		
Features	:	Omni-Directional Radiation Pattern Collinear 3.5 dBi Peak Gain Efficiency > 61% Robust Design for all Weather operation IP65 Waterproof Length: 320mm, Weight: 350g Connector: N-type Female Wall/Pole Mount Bracket Included RoHS compliant		





1.Introduction

The OMB.915.B03F21 is a fiberglass omnidirectional outdoor antenna, operating in the 902-915MHz ISM band, is designed to offer long distance coverage. The antenna is designed for applications such as metering, industrial / environmental monitoring, remote asset monitoring, and mesh network applications.

The OMB.915 operates at 915MHz, one of the most widely used license free ISM bands, with a 3.5dBi peak gain. The omnidirectional antenna radiates uniformly in the azimuth. This collinear design characteristic provides the best performance, giving optimized coverage and therefore longer range in the horizontal plane over 360 degrees, thus minimizing the amount of nodes needed for a mesh network.

The UV resistant fiberglass housing enables the OMB antenna to be utilized in all kinds of harsh environments, making it more robust and safer than traditional whip antennas. It can be connected directly to the access point or telemetry unit, or can be mounted on wall or device surface via the N-type connector.



2. Specification

ELECTRICAL						
Standard	ISM 915					
Band	902~928MHz					
Antenna Type	Collinear					
Gain(max)	3.5dBi					
Polarization	Vertical					
Impedance	50 ohms					
Max Input Power	50 watts					
VSWR	<1.5:1					
Radiation	Omnidirectional					
Vertical Bandwidth	78 Deg					
Horizontal Bandwidth	360 Deg					
Antenna Design	Dipole Array					
Internal Material	Copper					
Connector	N Type Female					
MECHANICAL						
Length	320mm(Max)					
Bracket Dimension	70*35mm(Max)					
Radome Diameter	24mm					
Antenna Weight	280g					
Mounting Accessories	70g					
Application	Indoor/Outdoor					
Radome Material	White Fiberglass					
Base Material	Aluminum					
Mount Style	Pole Mount/Wall Mount					
Mounting	Stainless Steel					
Wind Resistance	>150mph (>241km/h)					
Waterproof	IP65					
ENVIRONMENTAL						
Storage Temperature	-40°C to +80°C					
Operating Temperature	-40°C to +60°C					
Operating Humidity	10%~90% non-condensing					
Storage Humidity	5%~90% non-condensing					



3.Antenna Characteristics

3.1 Return Loss



3.2 Maximum Gain





3.3 Average Gain



3.4 Efficiency





4.3D Radiation Property





XY Plane



XZ Plane





5. Drawing



Side View

U–Bolt



[Name	P/N	Material	Finish	QTY
	1	OMB.915 Antenna	001212B020021A	Glass Fiber	White	1
•	2	Cover	000111K000021A	ABS	Sliver	1
[3	Bracket	000311K000021A	Aluminum	Silver	1
	4	N Type(F)	201211K000021A	Brass	Ni Plated	1
	5	M6 U Bolt	000412B000021A	Stainless Steel	Sliver	1
[6	M6 Washer	000411K010021A	Stainless Steel	Silver	2
[7	M6 Nut	000411K020021A	Stainless Steel	Sliver	2









6. Packaging

1 OMB.915.B03F21 per tube Tube Dimensions - Ø80mm*Height 380mm Total Weight - 443g





7.Antenna Installation Guide





Taoglas makes no warranties based on the accuracy or completeness of the contents of this document and reserves the right to make changes to specifications and product descriptions at any time. Taoglas reserves all rights to this document and the information contained herein.

Reproduction, use or disclosure to third parties without express permission is strictly prohibited.

Copyright © Taoglas