



Connectors > Pluggable IO Connectors & Cages



Pluggable I/O Product Type: **Cage Assembly**

Data Rate (Max): **28 Gb/s**

Sealable: **No**

Number of Ports: **1**

Port Matrix Configuration: **1 x 1**

Features

Product Type Features

Thermal Accessory Type Included	Heat Sink
Cage Type	Single
Pluggable I/O Product Type	Cage Assembly
Sealable	No
Form Factor	QSFP28/56

Configuration Features

Number of Rear EONs per Port Column	2
Number of Ports	1
Port Matrix Configuration	1 x 1

Electrical Characteristics

Data Rate (Max)	28 Gb/s
-----------------	---------

Body Features

Heat Sink Finish	Anodized Black
	.256 in
Heat Sink Height Class	SAN
Heat Sink Style	Pin

Contact Features

PCB Contact Termination Area Plating Material	Tin
---	-----



Termination Features

Termination Post & Tail Length	2.05 mm[.081 in]
Termination Method to Printed Circuit Board	Through Hole - Press-Fit

Housing Features

Cage Material	Nickel Silver
---------------	---------------

Dimensions

PCB Thickness (Recommended)	1.57 mm[.062 in]
-----------------------------	------------------

Usage Conditions

Operating Temperature Range	-40 – 85 °C[-40 – 185 °F]
-----------------------------	---------------------------

Operation/Application

Pluggable I/O Applications	SFP+ Stacked Belly-to-Belly
Heat Sink Compatible	Yes
Circuit Application	Signal

Industry Standards

UL Flammability Rating	UL 94V-0
------------------------	----------

Packaging Features

Packaging Method	Box & Tray
------------------	------------

Other

Included Lightpipe	No
EMI Containment Feature Type	Internal/External EMI Springs

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2023 (235) Candidate List Declared Against: JUNE 2023 (235) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free



Solder Process Capability

Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

 TE Part # CAT-C11-Z806726 QSFP28 to QSFP28 Cable Assembly: 30 AWG	 TE Part # CAT-C11-N49 QSFP28-Two QSFP28 Cable Assembly: 30 AWG	 TE Part # CAT-C11-Z8 QSFP28 to QSFP28 Cable Assembly: 26 AWG	 TE Part # CAT-C11-N490333 QSFP28-Four SFP+ Cable Assembly: 30 AWG
 TE Part # CAT-C11-N490325 QSFP28-Four SFP+ Cable Assembly: 26 AWG	 TE Part # CAT-Q17-N490325 QSFP56 to QSFP56 Cable Assembly: 30 AWG	 TE Part # CAT-Q17-N49033 QSFP56-Two QSFP56 Cable Assembly: 30 AWG	 TE Part # CAT-C11-Q17 QSFP56 to QSFP56 Cable Assembly: 26 AWG
 TE Part # CAT-Q17-N49011 QSFP56-Four SFP56 Cable Assembly: 30 AWG	 TE Part # CAT-Q17-N490333 QSFP56-Four SFP56 Cable Assembly: 26 AWG	 TE Part # 1888810-2 EMI/Dust Cover,XFP And QSFP	 TE Part # 1551920-2 zQSFP+ connector assembly



TE Part # 6-2215048-1
ASSY, SEATING TL, QSFP28, 1X1

Also in the Series | zQSFP+/QSFP28

Heat Sinks(1)

Pluggable I/O Cable Assemblies(81)

Pluggable IO Connectors & Cages(425)

Customers Also Bought

TE Part #2274001-1
ZSFP+ 1X1 CAGE ASSEMBLY
PRESSFIT

TE Part #5352115-1
Z-PACK/C RAF 55P

TE Part #1761008-3
SFP 1X4 CAGE & LIGHT PIPE KIT

TE Part #5750069-1
Mini DIN, 4 pos, R/A, Shield

TE Part #5520252-4
MJ,R/A,8P/8C,P/NL STOPS,KEYED

TE Part #5650913-5
ASSY,PIN,EUROCARD,TYPE C,LEAD-

TE Part #2176350-6
CRGCQ 2512 6R8 5%

TE Part #1-103168-4
32 MODII HDR DRST SHRD .100CL

TE Part #8-1747981-2
Std HDMI, RA, SMT, Panel grd, Flange



Documents

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_2170704-2_A.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_2170704-2_A.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_2170704-2_A.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

QSFP28/56 and zQSFP+ Interconnects

English

Product Specifications

Application Specification

English