




TE Internal #: 2232902-1  
Receptacle Contact, Tin, 300 VAC, Locking Lance Contact  
Retention, 26 – 22 AWG Wire Size, .13 – .33 mm² Wire Size, Crimp,  
Copper Alloy, Power  
[View on TE.com >](#)

Connectors > Contacts > Connector Contacts > Power Double Lock Receptacle



Contact Type: **Receptacle**  
Contact Mating Area Plating Material: **Tin**  
Wire Contact Termination Area Plating Material: **Pre-Tin**  
Operating Voltage: **300 VAC**  
Contact Retention Within Housing: **With**

[All Power Double Lock Receptacle \(6\)](#)

Features

Product Type Features

Discrete Wire Type	Stranded
--------------------	----------

Electrical Characteristics

Operating Voltage	300 VAC
-------------------	---------

Contact Features

Mating Tab Width	1.5 mm[.06 in]
Mating Tab Thickness	.5 mm[.02 in]
Wire Contact Termination Area Plating Thickness	.8 µm[31.49 µin]
Wire Contact Termination Area Plating Material Finish	Bright
Contact Orientation	Straight
Contact Type	Receptacle
Contact Mating Area Plating Material	Tin
Wire Contact Termination Area Plating Material	Pre-Tin
Contact Retention Within Housing	With



Contact Base Material	Copper Alloy
Contact Current Rating (Max)	5 A

Termination Features

Termination Method to Wire & Cable	Crimp
Product Terminates To	Wire & Cable

Mechanical Attachment

Wire Insulation Support	With
Contact Retention Type Within Housing	Locking Lance

Dimensions

Compatible Insulation Diameter Range	1.3 – 2 mm[.051 – .079 in]
Wire Size	.13 – .33 mm²

Usage Conditions

Operating Temperature Range	-30 – 105 °C[-22 – 221 °F]
-----------------------------	----------------------------

Operation/Application

Circuit Application	Power
---------------------	-------

Packaging Features

Packaging Quantity	5000
Packaging Method	Reel

Product Compliance

For compliance documentation, visit the product page on TE.com>













EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2023 (235) Candidate List Declared Against: JUNE 2023 (235) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not reviewed for solder process capability

Product Compliance Disclaimer




This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

 <p>TE Part # 917354-1 AMP POWER D/LOCK PLUG HDR 12P</p>	 <p>TE Part # CAT-P87024-P729 STD Temp Power Double Lock Plug</p>	 <p>TE Part # CAT-P87024-P729A Glow Wire Power Double Lock Plug</p>	 <p>TE Part # 2305570-1 Strip Terminal Cutter-Side Feed-No Crimp</p>
 <p>TE Part # 2836138-1 OCEAN_2.0_Applicator-S-055F108OV</p>	 <p>TE Part # 2836138-2 OCEAN_2.0_Applicator-S-055F108OV</p>	 <p>TE Part # 5-368571-1 FOAMING PROOF PLUG 3POS NAT</p>	 <p>TE Part # 5-368571-2 FOAMING PROOF PLUG 3POS RED</p>
 <p>TE Part # 5-368571-4 FOAMING PROOF PLUG 3POS YEL</p>	 <p>TE Part # 2108960-1 DISTRIBUTION CONNECTOR</p>	 <p>TE Part # 2367063-1 POWER DBL LOCK PLUG HSG 2P</p>	 <p>TE Part # 2475668-1 PDL10P PLUG HOUSING 3.96MM,DBL ROW (GWT)</p>

Customers Also Bought



Documents

Product Drawings

AMP POWER DBL LOCK REC (S)

English

CAD Files

3D PDF

3D

Customer View Model

ENG\_CVM\_CVM\_2232902-1\_B.2d\_dxf.zip

English

Customer View Model

ENG\_CVM\_CVM\_2232902-1\_B.3d\_igs.zip

English

Customer View Model

ENG\_CVM\_CVM\_2232902-1\_B.3d\_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications

Application Specification

English