




Connectors > Contacts > Connector Contacts



Contact Type: **Socket**
Contact Mating Area Plating Material: **Tin**
Wire Contact Termination Area Plating Material: **Pre-Tin**
Operating Voltage: **600 VDC**

Features

Product Type Features

Discrete Wire Type	Stranded
--------------------	----------

Electrical Characteristics

Operating Voltage	600 VDC
-------------------	---------

Contact Features

Mating Pin Diameter	1 mm[.039 in]
Wire Contact Termination Area Plating Thickness	.4 µm[15.74 µin]
Wire Contact Termination Area Plating Material Finish	Bright
Contact Orientation	Straight
Contact Type	Socket
Contact Mating Area Plating Material	Tin
Wire Contact Termination Area Plating Material	Pre-Tin
Contact Retention Within Housing	With
Contact Base Material	Phosphor Bronze
Contact Current Rating (Max)	11.2 A



Termination Features

Termination Method to Wire & Cable	Crimp
Product Terminates To	Wire & Cable

Mechanical Attachment

Wire Insulation Support	Without
-------------------------	---------

Dimensions

Compatible Insulation Diameter Range	1.19 – 1.75 mm[.047 – .069 in]
Wire Size	.12 – .4 mm²

Usage Conditions

Operating Temperature Range	-55 – 105 °C[-67 – 221 °F]
-----------------------------	----------------------------

Operation/Application

Circuit Application	Power
---------------------	-------

Industry Standards

Compatible With Agency/Standards Products	CSA, UL
UL Flammability Rating	UL 94V-0

Packaging Features

Packaging Quantity	7000
Packaging Method	Reel

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2023 (235) Candidate List Declared Against: JUNE 2023 (235) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer



This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

TE Part # CAT-AM71-C83998EE Mini Circular Plastic Connectors (CPC)	TE Part # 91529-1 CCII MINI-UMNL PIN 26-22 ASSY	TE Part # 90758-2 PROCrimp DIE MINI UNIV MNL	TE Part # 770586-1 22P MINI UMNL PLUG HSG
TE Part # 794942-1 10P MINI UMNL CAP HSG	TE Part # 770587-1 24P MINI UMNL PLUG HSG	TE Part # 770582-1 14P MINI UMNL PLUG HSG	TE Part # 770585-1 20P MINI UMNL PLUG HSG
TE Part # 172333-1 MINI UNIVERSAL M-N-L HOUSING	TE Part # 794781-1 10P MINI UMNL PLUG HSG	TE Part # 794941-1 08P MINI UMNL CAP HSG	TE Part # 794895-1 6 CIR MINI UMNL RND WIRE HOLES
TE Part # 794821-1 08P MINI UMNL PLUG HSG	TE Part # 794940-1 06P MINI UMNL CAP HSG	TE Part # 770581-1 12P MINI UMNL PLUG HSG	TE Part # 770580-1 10P MINI UMNL PLUG HSG



TE Part # 770584-1
18P MINI UMNL PLUG HSG



TE Part # 172328-1
MINI UNIVERSAL MATE-N-LOK CAP HOUSING 2P



TE Part # 172330-1
MINI UNIVERSAL MATE-N-LOK CAP HOUSING 4P



TE Part # 172344-1
MINI UNIVERSAL MATE-N-LOK CAP HOUSING 3P

Also in the Series | Mini-Universal MATE-N-LOK



Connector Caps & Covers(2)



Connector Contacts(92)



Connector Hardware(4)




Connector Seals & Cavity Plugs(17)



Connector Strain Relief(2)



Insertion & Extraction Tools(1)




PCB Headers & Receptacles(1)




Rectangular Power Connectors(197)

Customers Also Bought




TE Part #5499160-6
A/L UNIV HDR 26P VERT SHT LAT




TE Part #292133-2
CT P/HDR ASSY BOX V 2P W/O KIN



TE Part #6-1393211-6
T92P7D12-24



TE Part #2-179694-2
2MM CT MT REC ASSY 2P GRAY




TE Part #1-1734839-2
FPC CONN. 0.5MM PITCH T/C,12P



TE Part #3-794627-4
04P MICRO MNL ASSY,RA ,SMT, LF



TE Part #292303-3
Std USB Type A, R/A, T/H, Natural



TE Part #1-770621-0
12P MINI UMNL DBL ROW HDR ASSY



Documents

Product Drawings

MINI UMNL SOCK 26-22 AWG SN

English

CAD Files

Customer View Model

ENG_CVM_CVM_770902-4_T.2d_dxf.zip

English

3D PDF

3D

Customer View Model

ENG_CVM_CVM_770902-4_T.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_770902-4_T.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

AMP Circular Connectors for Commercial Signal & Power Applications Continued

English

SOFT_SHELL_PIN_AND_SOCKET_CONNECTORS_CATALOG

English

Product Specifications

Product Specification

English

Instruction Sheets

Instruction Sheet (U.S.)

English