




AMP-IN

TE Internal #: 170072-1
PCB Terminals, Receptacle, PCB Hole Diameter 1.83 mm [.072 in],
24 – 20 AWG Wire Size, .2 – .6 mm² Wire Size, Through Hole -
Solder, Pre-Tin Plating

[View on TE.com >](#)

Terminals & Splices > PCB Terminals



PCB Terminal Type: **Receptacle**
PCB Thickness (Recommended): **1.6 mm [.063 in]**
PCB Hole Diameter: **1.83 mm [.072 in]**
Profile Height from PCB: **6.8 mm [.271 in]**
Compatible Insulation Diameter (Max): **2.79 mm [.11 in]**

Features

Product Type Features

Terminal Features	Stud Hole
-------------------	-----------

Contact Features

Contact Underplating Material Thickness	.5 µm[19.68 µin]
Contact Mating Area Plating Material Thickness	.8 µm[31.5 µin]
PCB Terminal Type	Receptacle
Terminal Plating Material	Pre-Tin
Contact Underplating Material	Copper
Terminal Size	Standard
Terminal Orientation	Straight

Termination Features

Termination Method to Printed Circuit Board	Through Hole - Solder
Product Terminates To	Printed Circuit Board

Mechanical Attachment

Wire Insulation Support	With
-------------------------	------



Dimensions

Extension Below Board	3.6 mm[.141 in]
PCB Thickness (Recommended)	1.6 mm[.063 in]
PCB Hole Diameter	1.83 mm[.072 in]
Profile Height from PCB	6.8 mm[.271 in]
Compatible Insulation Diameter (Max)	2.79 mm[.11 in]
Compatible Insulation Diameter Range	1.52 – 2.79 mm[.06 – .11 in]
Wire Size	.2 – .6 mm²

Usage Conditions

Insulation Option	Uninsulated
Operating Temperature Range	-30 – 105 °C[-22 – 221 °F]

Packaging Features

Packaging Quantity	7000
Packaging Method	Reel

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2023 (235) Candidate List Declared Against: JUNE 2023 (235) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Wave solder capable to 240°C


Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits





as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

 TE Part # 3-42642-3 AMP-IN TERM IS 22-20 010PTBR	 TE Part # 154645-2 AMP-IN TERMINAL	 TE Part # 170072-6 AMP-IN KONTAKT	 TE Part # 2266586-2 OC-AT-S-FA-062F100F-001-0127
 TE Part # 2305570-1 Strip Terminal Cutter-Side Feed-No Crimp	 TE Part # 7-2266586-7 OC-062F100F-CRIMPTOOLINGKIT		

Customers Also Bought

 TE Part #3-1416100-2 ST3P3LC4	 TE Part #3-521057-2 ULTRAFAST 250 ASSY TAB 16-14 AWG TPBR	 TE Part #794184-1 02P MINI UMNL2 PLUG HSG UL94V0	 TE Part #9-1437719-6 T01-0580-S03-FEMALE REC PANEL MNT SOLDER
 TE Part #4426612006 RAYRIM-NR9-0-STK	 TE Part #TAX3882A202-004 RPC-M12X-8MS-3.0SH-M12X-8MR-TPE	 TE Part #2332956-1 LBF-A41150C	 TE Part #2345552-1 10096647



Documents

Product Drawings

AMP-IN 24-20 AWG

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_170072-1_V.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_170072-1_V.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_170072-1_V.3d_stp.zip

English

3D PDF

English

Customer View Model

ENG_CVM_170072-1_L1.2d_dxf.zip

English

Customer View Model

ENG_CVM_170072-1_L1.3d_igs.zip

English

Customer View Model

ENG_CVM_170072-1_L1.3d_stp.zip

English

By downloading the CAD file I accept and agree to the Terms and Conditions of use.

Product Specifications

Application Specification

English

Crimping AMP-IN Terminals

English

