




Connectors > Automotive Connectors > Automotive Connector Accessories > Other Automotive Connector Accessories



Automotive Connector Accessory Type: **Mounting Clip**

Primary Product Material: **PA**

Primary Product Color: **Black**

Operating Temperature Range: **-40 – 120 °C [-40 – 248 °F]**

Features

Product Type Features

Automotive Connector Accessory Type	Mounting Clip
-------------------------------------	---------------

Body Features

Primary Product Material	PA
Primary Product Color	Black

Usage Conditions

Operating Temperature Range	-40 – 120 °C[-40 – 248 °F]
-----------------------------	----------------------------

Industry Standards

UL Flammability Rating	UL 94HB
------------------------	---------

Packaging Features

Packaging Quantity	1000
Packaging Method	Bag

Other

Serviceable	Yes
-------------	-----

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold



EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2023 (235) Candidate List Declared Against: JUNE 2023 (235) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

TE Part # CAT-M8793-CH8172
MQS, CONNECTOR HOUSING

TE Part # 936142-1
JPT SEALED PLUG 6P ASSY(UEGO)

Also in the Series | Econoseal

Automotive Connector Caps & Covers
(1)


Automotive Connector Locks & Position Assurance(25)

Automotive Housings(86)


Automotive Terminals(43)



Connector Seals & Cavity Plugs(16)



Insertion & Extraction Tools(7)



Other Automotive Connector Accessories(5)




PCB Headers & Receptacles(3)



Primary Wire(1)

Customers Also Bought



TE Part #368049-1
E-J MK-II(+) 16P PLUG DBL



TE Part #1743161-2
CLIP HSG FOR 025 CONN 12P



TE Part #1-953042-6
31W HYB TIMER CONN



TE Part #968037-2
SPT A REC 6.3 Contact SWS Sn



TE Part #284853-2
12 POS FEMALE CONNECTOR ASS'Y



TE Part #936126-1
14POS MQS TAB




TE Part #936213-1
090III 18P CAP ASSY



TE Part #368036-1
CLIP FOR 070 & EJ MK-II(DAEWOO



TE Part #1452842-3
22 POS FEMALE HSG ASSY



TE Part #1-2349482-1
4 POS DIA 2.5 SOCKET CONNECTOR HSG

Documents



Product Drawings

CLIP FOR EJ MK-II (TREE TYPE)

English

CAD Files

Customer View Model

ENG_CVM_CVM_368373-1_O.2d_dxf.zip

English

3D PDF

3D

Customer View Model

ENG_CVM_CVM_368373-1_O.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_368373-1_O.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Instruction Sheets

Instruction Sheet (U.S.)

English