



Connectors > Rectangular Connectors > Rectangular Connector Housings



Connector System: Wire-to-Board, Wire-to-Panel, Wire-to-Wire

Number of Positions: 4

Centerline (Pitch): 4.39 mm [.17 in]

Number of Rows: 4

Housing Material: Polyester GF

Features

Product Type Features

Compatible With Discrete Wire Type	Stranded
Connector System	Wire-to-Board, Wire-to-Panel, Wire-to-Wire
Connector & Housing Type	Plug
Sealable	No

Configuration Features

Compatible With Wire & Cable Type	Discrete Wire
Number of Positions	4
Number of Rows	4

Electrical Characteristics

Operating Voltage	600 VAC
-------------------	---------

Contact Features

Contact Type	Socket
Contact Current Rating (Max)	13 A



Mechanical Attachment

Panel Mount Feature Type	Screw Mount
Connector Mounting Type	Panel Mount

Housing Features

Housing Color	Black
Centerline (Pitch)	4.39 mm[.17 in]
Housing Material	Polyester GF

Dimensions

Panel Thickness (Recommended)	.8 – 2.3 mm[.031 – .091 in]
	1.54 in
Row-to-Row Spacing	4.39 mm[.173 in]

Usage Conditions

Operating Temperature Range	-55 – 130 °C[-67 – 266 °F]
-----------------------------	----------------------------

Operation/Application

Circuit Application	Power & Signal
---------------------	----------------

Industry Standards

Compatible With Agency/Standards Products	CSA, UL, VDE
Compatible With Approved Standards Products	UL E28476
UL Flammability Rating	UL 94V-0

Packaging Features

Packaging Quantity	1
Packaging Method	Package

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2023 (235) Candidate List Declared Against: JUNE 2023 (235) Does not contain REACH SVHC



Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Wave solder capable to 265°C

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts




TE Part # 208211-4
SCREW,SHOULDER,SPECIAL



TE Part # 212609-1
RECEPT HSG,4 POSN,METRIMATE

Also in the Series | AMP Metrimate




Connector Caps & Covers(5)



Connector Hardware(4)



Insertion & Extraction Tools(1)



PCB Headers & Receptacles(83)



Rectangular Connector Housings(35)



Rectangular Contact Inserts(4)



Rectangular Power Connectors(2)



Standard Rectangular Connectors(5)



Customers Also Bought




TE Part #215083-8
MICRO-MATCH MOW.08P



TE Part #166053-1
COSI PIN CONTACT HD20 DF; 24-20 AWG



TE Part #350720-4
09P UMNL PLUG HSG UL94VO



TE Part #163087-8
062 SOC.ASS. TYP3+



TE Part #926882-3
UMNL SOK PTPPHBZ



TE Part #926887-3
UNIV.M-N-L.PIN



TE Part #350654-1
UMNL GRND PIN 20-14 PTPBR



TE Part #61795-1
RING 18-14 AWG TPST



TE Part #200389-2
GUIDE PIN KIT

Documents

Product Drawings

PLUG HSG,4 POSN,METRIMATE

English

CAD Files

Customer View Model

ENG_CVM_212608-1_B.3d_igs.zip

English

Customer View Model

ENG_CVM_212608-1_B.3d_stp.zip

English

Customer View Model

ENG_CVM_212608-1_B.2d_dxf.zip

English

3D PDF

English

3D PDF



3D

Customer View Model

[ENG_CVM_CVM_212608-1_K.2d_dxf.zip](#)

English

Customer View Model

[ENG_CVM_CVM_212608-1_K.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_212608-1_K.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

[METRIMATE_PIN_SOCKET_CATALOG](#)

English

Product Specifications

[Application Specification](#)

English

Agency Approvals

[Agency Approval Document](#)

English