



Power Triple Lock

TE Internal #: 1971782-2


Tab Contact, Tin, 600 VAC, 600 VDC, 14 AWG Wire Size, 2 mm²

Wire Size, Crimp, Copper Alloy, Power, -67 – 302 °F [-55 – 150 °C],

Power Triple Lock

[View on TE.com >](#)

Connectors > Contacts > Connector Contacts > Tab Contact — POWER TRIPLE LOCK



Contact Type: **Tab**

Contact Mating Area Plating Material: **Tin**

Wire Contact Termination Area Plating Material: **Pre-Tin**

Operating Voltage: **600 VDC**

[All Tab Contact — POWER TRIPLE LOCK \(12\)](#)

Features

Electrical Characteristics

Operating Voltage	600 VDC
-------------------	---------

Contact Features

Mating Tab Width	2.7 mm[.106 in]
Mating Tab Thickness	1.63 mm[.064 in]
Wire Contact Termination Area Plating Thickness	.8 – 1.5 µm[31.49 – 59 µin]
Wire Contact Termination Area Plating Material Finish	Bright
Contact Orientation	Straight
Contact Type	Tab
Contact Mating Area Plating Material	Tin
Wire Contact Termination Area Plating Material	Pre-Tin
Contact Retention Within Housing	Without
Contact Base Material	Copper Alloy
Contact Current Rating (Max)	15 A



Termination Features

Termination Method to Wire & Cable	Crimp
Product Terminates To	Wire & Cable

Mechanical Attachment

Wire Insulation Support	With
-------------------------	------

Dimensions

Compatible Insulation Diameter Range	3.4 – 3.7 mm[.134 – .146 in]
Wire Size	2 mm²

Usage Conditions

Operating Temperature Range	-55 – 150 °C[-67 – 302 °F]
-----------------------------	----------------------------

Operation/Application

Circuit Application	Power
---------------------	-------

Industry Standards

Compatible With Agency/Standards Products	UL, VDE
---	---------

Packaging Features

Packaging Method	Reel
------------------	------

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2023 (235) Candidate List Declared Against: JUNE 2023 (235) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not reviewed for solder process capability


Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent



chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

 TE Part # CAT-P87074-C1701A POWER TRIPLE LOCK High Temperature Caps	 TE Part # 1452426-1 EXTRACTION TOOL	 TE Part # 2151742-1 OCEAN_2.0_APPLICATOR-S-090F160F	 TE Part # 2151742-2 OCEAN_2.0_APPLICATOR-S-090F160F
 TE Part # 2217266-1 SDE COMMERCIAL TOOL AND DIE	 TE Part # 2217266-2 SDE COMMERCIAL TOOL AND DIE	 TE Part # 2305570-1 Strip Terminal Cutter-Side Feed-No Crimp	 TE Part # 7-2151742-1 OCEAN_2.0_APPLICATOR-S-090F160F
 TE Part # 7-2151742-2 OCEAN_2.0_APPLICATOR-S-090F160F	 TE Part # 7-2151742-7 OCEAN_2.0_SPARE_PART_KIT-090F160F		

Also in the Series | Power Triple Lock

 Connector Contacts(30)	 Connector Hardware(12)	 Insertion & Extraction Tools(1)	 Rectangular Power Connectors(300)
---	--	--	--



Customers Also Bought



TE Part #1-1744074-1
11P SL LID HSG W/O RAMP SPECIAL CL



TE Part #5-1971772-2
POWER TRIPLE LOCK High Temperature Caps



TE Part #1971777-3
PTL TPA HIGH TEMP 1 x 3 BLACK



TE Part #1971783-2
Receptacle Contact — POWER TRIPLE LOCK



TE Part #1971784-2
PTL TAB CONTACT, 16-19 AWG, 2X22 AWG



TE Part #42404-1
250 FASTON FLAG REC 18-12 AWG NPST



TE Part #42722-1
RING TONGUE 12-10 AWG BR



TE Part #1897058-1
CONNECTOR .125/.250 SERIES

Documents

Product Drawings

PTL TAB CONTACT, 14 AWG

English

PTL TAB CONTACT, 14 AWG

English

PTL TAB CONTACT, 14 AWG

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_1971782-2_E.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_1971782-2_E.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_1971782-2_E.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

1-1773734-9 TE Power Triple Lock Quick Reference Guide - German

German



9-1773465-1Power Triple Lock QRG

English

Product Specifications

Application Specification

English

Instruction Sheets

Instruction Sheet (U.S.)

English

Agency Approvals

VDE Certificate

English

VDE Certificate

English