

Specification Sheet

Part Number: 157-00401



- Mount provides low insertion and high extraction forces which makes for a strong and easy installation.
- Tie utilizes a strong hinge between the stud mount and strap head to provide superior holding ability.
- Clamping rails increase grip on round bundles.
- Thinner strap provides increased flexibility for improved ergonomics.

Wide Strap Cable Tie with .25" Stud Mount, 12.7" Long, 0.5" Wide, PA66HIRHSUV, Black, 300/bg

Article Number	157-00401
Type	WSI250
Color	Black (BK)
Quantity Per	bag
Product Description	Wide Strap Heavy Duty Cable Ties features a stud mount for direction application onto a 1/4" threaded stud. The tie is 0.5" wide, and handles bundles from 0.38 - 4.2". The low profile mount design engages a minimum of 4 threads on the stud which makes it easier to apply additional mounts onto one stud.
Short Description	Wide Strap Cable Tie with .25" Stud Mount, 12.7" Long, 0.5" Wide, PA66HIRHSUV, Black, 300/bg

Global Part Name	WSI250-PA66HIRHSUV-BK
------------------	-----------------------

Minimum Tensile Strength (Imperial)	120.0
-------------------------------------	-------

Minimum Tensile Strength (Metric)	535
-----------------------------------	-----

Length L (Imperial)	12.7
---------------------	------

Length L (Metric)	322.6
-------------------	-------

Fixation Method	Stud Mount
-----------------	------------

Identification Plate Position	none
-------------------------------	------

Releasable Closure	No
--------------------	----

Tie Closure	plastic pawl
-------------	--------------

Variant	Inside Serrated
---------	-----------------

Width W (Imperial)	0.5
--------------------	-----

Width W (Metric)	12.7
------------------	------

Bundle Diameter Min (Imperial)	0.38
--------------------------------	------

Bundle Diameter Min (Metric)	9.5
------------------------------	-----

Bundle Diameter Max (Imperial)	3.25
--------------------------------	------

Bundle Diameter Max (Metric)	82.5
------------------------------	------

Stud Diameter (Metric)	M6
Stud Diameter (Imperial)	1/4
Material	Polyamide 6.6 high impact modified, heat and UV stabilized (PA66HIRHSUV)
Material Shortcut	PA66HIRHSUV
Flammability	UL 94 HB
UV Resistant (Yes/No)	Yes
Operating Temperature	-40°F to +221°F (-40°C to +105°C)
Reach Compliant (Article 33)	Yes
ROHS Compliant	Yes
Package Quantity (Imperial)	300
Package Quantity (Metric)	300
Customs Number	3926909988

About HellermannTyton

HellermannTyton is a global manufacturer of cable management and identification solutions for automotive, solar,

electrical, construction, industrial automation, broadband and other OEM markets. The company's integrated approach to product design, sustainability, production, quality assurance and delivery is optimized to benefit local and global customers. HellermannTyton operates in 39 countries, with North American headquarters in Milwaukee, Wisconsin. (www.hellermann.tyton.com).