



Terminals & Splices > Automotive Terminals > TIMER, RECEPTACLE AND TAB



Terminal Type: **Receptacle**
Mating Tab Width: **2.8 mm [.11 in]**
Mating Tab Thickness: **.8 mm [.031 in]**
Terminal Transmits: **0 – 24 A (Low Power)**
Wire Size: **20 – 17 AWG**

[All TIMER, RECEPTACLE AND TAB \(330\)](#)

Features

Product Type Features

Receptacle Style	180°
Sealable	No
Primary Locking Feature	Locking Lance

Contact Features

Contact Size	2.8mm
Contact Fabrication	Stamped & Formed
Wire Contact Termination Area Plating Material	Tin
Typical Current Rating	10 A
Crimp Type	F-Crimp
Terminal Type	Receptacle
Mating Tab Width	2.8 mm[.11 in]
Mating Tab Thickness	.8 mm[.031 in]
Interface Plating	Tin (Sn)

Termination Features

Termination Method to Wire & Cable	Crimp
Product Terminates To	Wire

Dimensions



Compatible Insulation Diameter Range	2 – 2.7 mm[.079 – .106 in]
Wire Size	.5 – 1 mm²
Wire Size Search	17 AWG, 18 AWG, 19 AWG, 20 AWG

Usage Conditions

Insulation Option	Uninsulated
Operating Temperature (Max)	80 °C, 85 °C, 90 °C, 100 °C, 105 °C, 110 °C [176 °F][185 °F][194 °F][212 °F][221 °F][230 °F]
Operating Temperature Range	-40 – 110 °C[-40 – 230 °F]

Operation/Application

Compatible With Wire Base Material	Copper
------------------------------------	--------

Industry Standards

Compatible With Agency/Standards Products	IEC 664/664A (DIN VDE 0110)
---	-----------------------------

Packaging Features

Packaging Quantity	4000
Packaging Method	Carton

Other

Terminal Transmits	0 – 24 A (Low Power)
--------------------	----------------------

Product Compliance

For compliance documentation, visit the product page on TE.com>



EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2023 (235) Candidate List Declared Against: JUNE 2023 (235) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer





This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts




 TE Part # 1-1579007-4 EXTRACTION TOOL	 TE Part # 4-1579007-3 EXTRACTION TOOL KIT	 TE Part # 963325-1 25P J-T GRIFFSCHALE	 TE Part # 2151264-2 OCEAN_2.0_APPLICATOR-S-080F130F
 TE Part # 2305570-1 Strip Terminal Cutter-Side Feed-No Crimp	 TE Part # 7-2151264-2 OCEAN_2.0_APPLICATOR-S-080F130F	 TE Part # 7-2151264-7 OCEAN_2.0_SPARE_PART_KIT-080F130F	 TE Part # 827249-1 25 POS. MINI SPRING RECPT. HSG

Also in the Series | Junior Timer

 Automotive Housings(60)	 Automotive Terminals(15)	 PCB Headers & Receptacles(2)
--	--	---

Customers Also Bought



 TE Part #963120-1 8P JUNIOR TIMER HOUSING	 TE Part #179093-6 040/070 MK-2 PLUG ASSY 16P	 TE Part #963768-1 TAB 9.5x1.2 CONTACT CS SRC Sn	 TE Part #3-1813099-3 2.5mm SOCKET HSG ASSEMBLY (GREEN 2POS)
 TE Part #1379659-3 8W PLUG HOUSING ASSY BLUE	 TE Part #444430-1 SINGLE WIRE SEAL	 TE Part #1801617-1 FUSES AND RELAYS HOLDER 6 MINIFUSES	 TE Part #2295763-1 MICRORELAY HOLDER ASSEMBLY
 TE Part #1813337-2 TEH-NO.3-0-50MM	 TE Part #2424195-9 HSD CABLE ASSEMBLY		

Documents

Product Drawings
JUNIOR-TIMER KONT

German

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_927863-1_B_c-927863-1-b.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_927863-1_B_c-927863-1-b.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_927863-1_B_c-927863-1-b.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages



Timer Interconnection System

English

Product Specifications

Application Specification

English