



Terminals & Splices > Crimp Wire Pins, Tabs & Ferrules



Crimp Wire Terminal Type: Pin

Wire Size: 2048 – 5178 CMA

Barrel Inside Diameter: 2.24 mm [.088 in]

Features

Product Type Features

| | |
|------------------------------------|----------|
| Compatible With Discrete Wire Type | Stranded |
|------------------------------------|----------|

Configuration Features

| | |
|-----------------------------------|---------------|
| Compatible With Wire & Cable Type | Discrete Wire |
|-----------------------------------|---------------|

Contact Features

| | |
|---------------------------|----------|
| Crimp Wire Terminal Type | Pin |
| Barrel Type | Open |
| Terminal Plating Material | Unplated |
| Terminal Orientation | Straight |

Mechanical Attachment

| | |
|-------------------------|---------|
| Wire Insulation Support | Without |
|-------------------------|---------|

Dimensions

| | |
|-----------------------------|-------------------|
| Wire Size | 2048 – 5178 CMA |
| Barrel Inside Diameter | 2.24 mm [.088 in] |
| Terminal Material Thickness | .33 mm [.013 in] |
| Overall Product Length | 7 mm [.275 in] |

Usage Conditions



| | |
|-------------------|-------------|
| Insulation Option | Uninsulated |
|-------------------|-------------|

Packaging Features

| | |
|--------------------|-------|
| Packaging Quantity | 25000 |
| Packaging Method | Reel |

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

| | |
|---|---|
| EU RoHS Directive 2011/65/EU | Compliant |
| EU ELV Directive 2000/53/EC | Compliant |
| China RoHS 2 Directive MIIT Order No 32, 2016 | No Restricted Materials Above Threshold |
| EU REACH Regulation (EC) No. 1907/2006 | Current ECHA Candidate List: JUNE 2023 (235) Candidate List Declared Against: JUNE 2023 (235) Does not contain REACH SVHC |
| Halogen Content | Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free |
| Solder Process Capability | Not applicable for solder process capability |

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts


TE Part # 2150230-1
OCEAN_2.0_Applicator-E-100F

TE Part # 2150230-2
OCEAN_2.0_Applicator-E-100F

TE Part # 539688-2
MATRIZE MINI-UMNL

TE Part # 7-2150230-7
OCEAN_2.0_SPARE_PART_KIT-100F

Customers Also Bought




TE Part #5069844021
CGPT-6.4/3.2-0-SP




TE Part #794184-1
02P MINI UMN2 PLUG HSG UL94V0



TE Part #42007
RING 190(4.82MM) TERMINAL 18-14
AWG TPBR




TE Part #925856-2
WIRE PIN 15.5-13.5 AWG .01 BR



TE Part #925553-1
AM WIRE PIN 17-13 .013 BR



TE Part #5677584004
RNF-3000-9/3-0-SP




TE Part #5-928999-6
MQS0,63 Ag rec LL unseal. >0,2-0,35



TE Part #4-459736-1
CRIMPER, WIRE "F" SPLICE TYPE



TE Part #1320928-2
STRIP GUIDE



TE Part #2217901-1
KIT, REBUILD, AIR FEED

Documents

Product Drawings

[AM WIRE PIN 17-13 .013 BR](#)

English

CAD Files

[3D PDF](#)

3D

Customer View Model

[ENG_CVM_CVM_926824-1_D.2d_dxf.zip](#)

English

Customer View Model

[ENG_CVM_CVM_926824-1_D.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_926824-1_D.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.



[Product Specifications](#)

[Application Specification](#)

English