

Article No. : 6SL3230-3YC12-0UB0



Figure similar

Client order no. :
Order no. :
Offer no. :
Remarks :

Item no. :
Consignment no. :
Project :

Rated data

Input

| | | |
|----------------------|---------------------------|-----------------|
| Number of phases | 3 AC | |
| Line voltage | 200 ... 240 V +10 % -20 % | |
| Line frequency | 47 ... 63 Hz | |
| Rated voltage | 200V IEC | 240V NEC |
| Rated current (LO) | 5.40 A | 5.40 A |
| Rated current (HO) | 3.80 A | 3.80 A |

Output

| | | |
|-------------------------------------|-----------------|-------------------------------|
| Number of phases | 3 AC | |
| Rated voltage | 200V IEC | 240V NEC ¹⁾ |
| Rated power (LO) | 1.10 kW | 1.50 hp |
| Rated power (HO) | 0.75 kW | 1.00 hp |
| Rated current (LO) | 6.00 A | 6.00 A |
| Rated current (HO) | 4.20 A | 4.20 A |
| Rated current (IN) | 6.10 A | |
| Max. output current | 8.10 A | |
| Pulse frequency | 4 kHz | |
| Output frequency for vector control | 0 ... 200 Hz | |
| Output frequency for V/f control | 0 ... 550 Hz | |

Overload capability

Low Overload (LO)
110% base load current IL for 60 s in a 300 s cycle time

High Overload (HO)
150% x base load current IH for 60 s within a 600 s cycle time

General tech. specifications

| | |
|-----------------------------------|-------------------------------------------|
| Power factor λ | 0.70 ... 0.85 |
| Offset factor $\cos \phi$ | 0.96 |
| Efficiency η | 0.95 |
| Sound pressure level (1m) | 55 dB |
| Power loss ³⁾ | 0.084 kW |
| Filter class (integrated) | Unfiltered |
| EMC category (with accessories) | without |
| Safety function "Safe Torque Off" | without SIRIUS device (e.g. via S7-1500F) |

Communication

Communication USS, Modbus RTU, BACnet MS/TP

Inputs / outputs

Standard digital inputs

| | |
|------------------------|-------|
| Number | 6 |
| Switching level: 0 → 1 | 11 V |
| Switching level: 1 → 0 | 5 V |
| Max. inrush current | 15 mA |

Fail-safe digital inputs

| | |
|--------|---|
| Number | 1 |
|--------|---|

Digital outputs

| | |
|------------------------------------|----------------|
| Number as relay changeover contact | 2 |
| Output (resistive load) | DC 30 V, 5.0 A |
| Number as transistor | 0 |

Analog / digital inputs

| | |
|------------|------------------------|
| Number | 2 (Differential input) |
| Resolution | 10 bit |

Switching threshold as digital input

| | |
|-------|-------|
| 0 → 1 | 4 V |
| 1 → 0 | 1.6 V |

Analog outputs

| | |
|--------|-------------------------|
| Number | 1 (Non-isolated output) |
|--------|-------------------------|

PTC/ KTY interface

1 motor temperature sensor input, sensors that can be connected PTC, KTY and Thermo-Click, accuracy ± 5 °C

Closed-loop control techniques

| | |
|-------------------------------------------|-----|
| V/f linear / square-law / parameterizable | Yes |
| V/f with flux current control (FCC) | Yes |
| V/f ECO linear / square-law | Yes |
| Sensorless vector control | Yes |
| Vector control, with sensor | No |
| Encoderless torque control | No |
| Torque control, with encoder | No |

Data sheet for SINAMICS G120X

Article No. : 6SL3230-3YC12-0UB0

Ambient conditions

| | |
|-----------------------------|----------------------------------------------------|
| Standard board coating type | Class 3C3, according to IEC 60721-3-3: 2002 |
| Cooling | Air cooling using an integrated fan |
| Cooling air requirement | 0.009 m ³ /s (0.325 ft ³ /s) |
| Installation altitude | 1,000 m (3,280.84 ft) |

Ambient temperature

| | |
|-----------|--------------------------------|
| Operation | -20 ... 45 °C (-4 ... 113 °F) |
| Transport | -40 ... 70 °C (-40 ... 158 °F) |
| Storage | -25 ... 55 °C (-13 ... 131 °F) |

Relative humidity

| | |
|----------------|----------------------------------------------------------------|
| Max. operation | 95 % At 40 °C (104 °F), condensation and icing not permissible |
|----------------|----------------------------------------------------------------|

Connections

Signal cable

| | |
|-------------------------|------------------------------------------------------|
| Conductor cross-section | 0.15 ... 1.50 mm ² (AWG 24 ... AWG 16) |
|-------------------------|------------------------------------------------------|

Line side

| | |
|-------------------------|------------------------------------------------------|
| Version | screw-type terminal |
| Conductor cross-section | 1.50 ... 2.50 mm ² (AWG 16 ... AWG 14) |

Motor end

| | |
|-------------------------|------------------------------------------------------|
| Version | Screw-type terminals |
| Conductor cross-section | 1.50 ... 2.50 mm ² (AWG 16 ... AWG 14) |

DC link (for braking resistor)

| | |
|---------------|--------------------------|
| PE connection | On housing with M4 screw |
|---------------|--------------------------|

Max. motor cable length

| | |
|------------|-------------------|
| Shielded | 150 m (492.13 ft) |
| Unshielded | 300 m (984.25 ft) |

Mechanical data


| | |
|----------------------|---------------------|
| Degree of protection | IP20 / UL open type |
| Frame size | FSA |
| Net weight | 3.3 kg (7.28 lb) |
| Dimensions | |
| Width | 73 mm (2.87 in) |
| Height | 232 mm (9.13 in) |
| Depth | 218 mm (8.58 in) |

Standards

| | |
|---------------------------|-------------------------------------------------------------|
| Compliance with standards | UL, cUL, CE, C-Tick (RCM), EAC, KCC, SEMI F47, REACH |
| CE marking | EMC Directive 2004/108/EC, Low-Voltage Directive 2006/95/EC |

Converter losses to IEC61800-9-2*

| | |
|------------------------------------------------------|--------|
| Efficiency class | IE2 |
| Comparison with the reference converter (90% / 100%) | 46.9 % |



The percentage values show the losses in relation to the rated apparent power of the converter.

The diagram shows the losses for the points (as per standard IEC61800-9-2) of the relative torque generating current (I) over the relative motor stator frequency (f). The values are valid for the basic version of the converter without options/components.

*converted values

¹⁾The output current and HP ratings are valid for the voltage range 220V-240V

³⁾Typical value. More information can be found in the element group "Converter losses to IEC 61800-9-2" in this datasheet.

Data sheet for SINAMICS G120X

Article No. : 6SL3230-3YC12-0UB0

Operator panel: Intelligent Operator Panel (IOP-2)

Screen

| | |
|-------------------|-----------------|
| Display design | LCD color |
| Screen resolution | 320 x 240 Pixel |

Mechanical data

| | |
|----------------------|--------------------|
| Degree of protection | IP55 / UL type 12 |
| Net weight | 0.134 kg (0.30 lb) |

Dimensions

| | |
|--------|---------------------|
| Width | 70.00 mm (2.76 in) |
| Height | 106.85 mm (4.21 in) |
| Depth | 19.65 mm (0.77 in) |

Ambient conditions

Ambient temperature

| | |
|-----------|----------------------------------------------------------------------|
| Operation | 0 ... 50 °C (32 ... 122 °F) 55 °C only with door installation kit |
|-----------|----------------------------------------------------------------------|

| | |
|---------|--------------------------------|
| Storage | -40 ... 70 °C (-40 ... 158 °F) |
|---------|--------------------------------|

| | |
|-----------|--------------------------------|
| Transport | -40 ... 70 °C (-40 ... 158 °F) |
|-----------|--------------------------------|

Relative humidity at 25°C during

| | |
|----------------|------|
| Max. operation | 95 % |
|----------------|------|

Approvals

| | |
|----------------------------|--------------------------|
| Certificate of suitability | CE, cULus, EAC, KCC, RCM |
|----------------------------|--------------------------|