

Specification Sheet

Part Number: 133-03836



Fir tree design provides low insertion force and high extraction force ideal for simple, secure performance in a 6.5 mm (+/-0.4) hole.

Standoff design secures the bundle away from the mounting hole and areas that could cause damage due to rubbing.

Clip can be installed by hand – no need for hardware or tools.

Standoff Bundling Clip, 1.4" Long, Panel Thickness 0.02 - 0.19mm, PA66HIRHS, Black, 1500/ctn

Article Number	133-03836
----------------	-----------

Type	SOC23SO18
------	-----------

Color	Black (BK)
-------	------------

Quantity Per	carton
--------------	--------

Product Description	Bundling clips are designed to provide simple and easy methods of securing cable bundles, hoses or pipes. They are fastened onto the tape bar using bundle or cable ties. The different fixing orientations allow tape clips to be used with a wide range of panel thicknesses and hole diameters. Standard bundling clips are available as well as standoff and stud mount versions.
---------------------	---

Short Description	Standoff Bundling Clip, 1.4" Long, Panel Thickness 0.02 - 0.19mm, PA66HIRHS, Black, 1500/ctn
-------------------	--

Global Part Name	SOC23SO18-PA66HIRHS-BK
------------------	------------------------

Length L (Imperial)	2.04
---------------------	------

Length L (Metric)	50.0
-------------------	------

Offset Length (Imperial)	0.889
--------------------------	-------

Offset Length (Metric)	22.6
------------------------	------

Fixation Method	Fir Tree
-----------------	----------

Width W (Imperial)	1.4
--------------------	-----

Width W (Metric)	35.56
------------------	-------

Height H (Imperial)	1.2
---------------------	-----

Height H (Metric)	31.2
-------------------	------

Panel Thickness Min (Imperial)	0.02
--------------------------------	------

Panel Thickness Max (Imperial)	0.19
--------------------------------	------

Panel Thickness Min (Metric)	0.6
------------------------------	-----

Panel Thickness Max (Metric)	4.7
------------------------------	-----

Mounting Hole Diameter D (Imperial)	0.24 - 0.27
-------------------------------------	-------------

Mounting Hole Diameter D (Metric)	6.1 - 6.9 mm
-----------------------------------	--------------

Mounting Hole Diameter D Min (Imperial)	0.24
---	------

Mounting Hole Diameter D Max (Imperial)	0.27
---	------

Mounting Hole Diameter D Max (Metric)	6.9
---------------------------------------	-----

Material	Polyamide 6.6, high impact modified, heat stabilized (PA66HIRHS)
----------	--

Material Shortcut	PA66HIRHS
-------------------	-----------

UV Resistant (Yes/No)	No
-----------------------	----

Operating Temperature	-40°F to +230°F (-40°C to +110°C)
-----------------------	-----------------------------------

Reach Compliant (Article 33)	Yes
------------------------------	-----

ROHS Compliant	Yes
----------------	-----

Package Quantity (Imperial)	1500
-----------------------------	------

Package Quantity (Metric)	1500
---------------------------	------

Customs Number	3926909988
----------------	------------

About HellermannTyton

HellermannTyton is a global manufacturer of cable management and identification solutions for automotive, solar, electrical, construction, industrial automation, broadband and other OEM markets. The company's integrated approach

to product design, sustainability, production, quality assurance and delivery is optimized to benefit local and global customers. HellermannTyton operates in 39 countries, with North American headquarters in Milwaukee, Wisconsin. (www.hellermann.tyton.com).

© 2024 HellermannTyton. All Rights Reserved.

[Contact Us](#)

[RoHS/WEEE Compliance](#)

[Disclaimer](#)

[Terms and Conditions](#)