

106137-2 ✓ ACTIVE

Z-PACK | Z-PACK 2mm HM


TE Internal #: 106137-2

PCB Mount Shroud, Gray, Glass Filled Polyester, 110 Position, Z-PACK 2mm HM

[View on TE.com >](#)



Connectors > Connector Accessories > Connector Caps & Covers



Connector Cover Type: **PCB Mount Shroud**

Primary Product Color: **Gray**

Primary Product Material: **Glass Filled Polyester**

Number of Positions: **110**

Operating Temperature (Max): **125 °C [257 °F]**

Features

Product Type Features

| | |
|----------------------|------------------|
| Connector Cover Type | PCB Mount Shroud |
|----------------------|------------------|

Configuration Features

| | |
|----------------|---|
| Number of Rows | 5 |
|----------------|---|

| | |
|---------------------|-----|
| Number of Positions | 110 |
|---------------------|-----|

Body Features

| | |
|-----------------------|------|
| Primary Product Color | Gray |
|-----------------------|------|

| | |
|--------------------------|------------------------|
| Primary Product Material | Glass Filled Polyester |
|--------------------------|------------------------|

Mechanical Attachment

| | |
|-----------------------|----------------------|
| Mating Alignment Type | Multi-Purpose Center |
|-----------------------|----------------------|

| | |
|------------------|------|
| Mating Alignment | With |
|------------------|------|

Housing Features

| | |
|--------------------|---------------|
| Centerline (Pitch) | 2 mm[.079 in] |
|--------------------|---------------|

Dimensions

| | |
|---------------|------------------|
| Product Width | 15.4 mm[.606 in] |
|---------------|------------------|

| | |
|--------------------|-------------------|
| Product Length | 49.9 mm[1.965 in] |
| Product Height | 13.46 mm[.53 in] |
| Row-to-Row Spacing | 2 mm[.079 in] |

Usage Conditions

| | |
|-----------------------------|----------------------------|
| Operating Temperature (Max) | 125 °C[257 °F] |
| Operating Temperature Range | -55 – 125 °C[-67 – 257 °F] |

Industry Standards

| | |
|------------------------|----------|
| UL Flammability Rating | UL 94V-0 |
|------------------------|----------|

Product Compliance

For compliance documentation, visit the product page on TE.com>

| | |
|---|--|
| EU RoHS Directive 2011/65/EU | Compliant |
| EU ELV Directive 2000/53/EC | Compliant |
| China RoHS 2 Directive MIIT Order No 32, 2016 | No Restricted Materials Above Threshold |
| EU REACH Regulation (EC) No. 1907/2006 | Current ECHA Candidate List: JUNE 2023 (235) Candidate List Declared Against: JUNE 2023 (235) Does not contain REACH SVHC |
| Halogen Content | Not Low Halogen - contains Br or Cl > 900 ppm. |
| Solder Process Capability | Not applicable for solder process capability |

Product Compliance Disclaimer


This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts




TE Part # 5100147-1
Z-PACK/A RAF 110P


Also in the Series | Z-PACK 2mm HM




Backplane Connector Housings(4)




Backplane Power Connectors(6)



Connector Caps & Covers(62)




Connector Contacts(2)




Connector Hardware(97)



Hard Metric Backplane Connectors (267)



High Speed Backplane Connectors(1)



Insertion & Extraction Tools(2)




Rectangular Power Connectors(87)

Customers Also Bought



TE Part #5100145-1
Z-PACK/B25 RAF 125P



TE Part #5106773-1
Z-PACK/A VF 110P



TE Part #535059-4
064 EURO TYPE C RECEPT AP ASSY




TE Part #650947-5
096 EURO TYPE C PIN ST ASSY




TE Part #6368062-4
2X4 OFFSET STK MJ,SHLD,G/Y
LED&GND



TE Part #6469048-1
HMZD 4PR RA HDR 80P ASSY LF



TE Part #3-100525-2
Z-PACK M.CODING KEY



TE Part #1-6450121-5
MBXL R/A HDR 16S+4P



TE Part #796136-2
ASSY, SMT BATTERY CONN



TE Part #5188647-1
Z-PACK/B M-HDR 125P

Documents

Product Drawings

Z-PACK/A SHRD.110P

English

CAD Files

3D PDF

3D

Customer View Model

[ENG_CVM_CVM_106137-2_B.2d_dxf.zip](#)

English

Customer View Model

[ENG_CVM_CVM_106137-2_B.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_106137-2_B.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications

Application Specification

English