




Power Key 5.0

TE Internal #: 1-1376390-2
Rectangular Power Connectors, Housing, Plug, Wire-to-Board, 4
Position, 5 mm [.197 in] Centerline, Wire & Cable, UL 94V-0, Power
Key 5.0

[View on TE.com >](#)

Connectors > Power Connectors > Rectangular Power > Rectangular Power Connectors > STD Temp Power Key Plug



Rectangular Power Connector Type: **Housing**
Connector & Housing Type: **Plug**
Connector System: **Wire-to-Board**
Number of Positions: **4**
Centerline (Pitch): **5 mm [.197 in]**

[All STD Temp Power Key Plug \(34\)](#)

Features

Product Type Features

Rectangular Power Connector Type	Housing
Connector & Housing Type	Plug
Connector System	Wire-to-Board
Sealable	No
Connector & Contact Terminates To	Wire & Cable

Configuration Features

Number of Positions	4
Number of Power Positions	4
Number of Signal Positions	0
Number of Rows	1

Electrical Characteristics

Operating Voltage	300 VAC
-------------------	---------



Contact Features

Contact Base Material	Copper Alloy
Contact Current Rating (Max)	10 A
Contact Retention Within Housing	Without
Contact Type	Receptacle

Termination Features

Termination Method to Wire & Cable	Crimp
------------------------------------	-------

Mechanical Attachment

Strain Relief	Without
Mating Alignment Type	Keyed
Mating Retention	With
Mating Alignment	With
Panel Mount Feature	Without
PCB Mount Retention	Without
Mating Retention Type	Latch
Connector Mounting Type	Cable Mount (Free-Hanging)

Housing Features

Centerline (Pitch)	5 mm[.197 in]
Housing Color	Red
Housing Material	Nylon 6/6 GF

Dimensions

Connector Height	9.6 mm[.378 in]
Product Width	16.2 mm[.638 in]
Product Length	25 mm[.984 in]
Compatible Insulation Diameter Range	1.7 – 3.1 mm[.067 – .122 in]
Wire Size	434.18 – 2466.91 CMA

Usage Conditions

Operating Temperature Range	-40 – 105 °C[-40 – 221 °F]
-----------------------------	----------------------------

Operation/Application

Circuit Application	Power & Signal
---------------------	----------------

Industry Standards

CSA Rating	LR 7189
------------	---------



UL Rating	Recognized
Compatible With Agency/Standards Products	CSA, UL
Compatible With Approved Standards Products	UL E28476
UL Flammability Rating	UL 94V-0
Glow Wire Rating	GWT 750°C (Without Flame)

Packaging Features

Packaging Quantity	500
Packaging Method	Bag

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2023 (235) Candidate List Declared Against: JUNE 2023 (235) Does not contain REACH SVHC
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 1-1376384-2
5mm B-T-W Conn. 4P HDR ASSEMBL

TE Part # CAT-P8704-P729
STD Temp Power Key Plug

TE Part # 1-1376390-5
5MM POWER KEY 4P PLUG HSG RED

TE Part # 1463644-1
EXT-TOOL,5.0 POWER KEY CONN.

Also in the Series | Power Key 5.0

Connector Contacts(4)

Connector Hardware(4)

Insertion & Extraction Tools(1)

Rectangular Power Connectors(107)

Customers Also Bought

TE Part #5-1971876-3
PTL 3X3 PLUG HSG HIGH TEMP KEY A LGR

TE Part #1971777-2
PTL TPA HIGH TEMP 1 x 2 BLACK

TE Part #1376396-1
5MM POWER KEY D/L PLATE GREEN

TE Part #1971785-2
Receptacle Contact — POWER TRIPLE LOCK

TE Part #5-1971875-3
PTL 3X3 CAP PANEL MT HITEMP KEY A LGR

TE Part #41808
RING TERMINAL 10-8 AWG TPCU

TE Part #F82626-000
SCT-NO.2-E5-0-40MM

TE Part #1969507-2
250 FASTON HSG.,FLAG,REC.,1 POS, NATURAL

TE Part #60487-1
187 FASTON REC 18-16 AWG BR



Documents

Product Drawings

5MM POWER KEY 4P PLUG HSG RED

English

5MM POWER KEY 4P PLUG HSG RED

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_1-1376390-2_F.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_1-1376390-2_F.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_1-1376390-2_F.3d_stp.zip

English

3D PDF

English

Customer View Model

ENG_CVM_1-1376390-2_B.2d_dxf.zip

English

Customer View Model

ENG_CVM_1-1376390-2_B.3d_igs.zip

English

Customer View Model

ENG_CVM_1-1376390-2_B.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

SOFT_SHELL_PIN_SOCKET_CONNECTORS_STANDARD_DENSITY

English

1-1773881-9 Power Key Connector Quick Reference Guide

English

Product Specifications

5.0 POWER KEY CONNECTOR

Japanese

Application Specification

Japanese

Instruction Sheets



[The extraction tool for 5MM Power Key Contact](#)

English

[Instruction Sheet \(non U.S.\)](#)

English

[Agency Approvals](#)

[VDE Certificate](#)

English