



Terminals & Splices > Automotive Terminals



Terminal Type: **Tab**
Mating Tab Width: **.8 mm [.031 in]**
Mating Tab Thickness: **.64 mm [.025 in]**
Terminal Transmits: **0 – 24 A (Low Power)**
Wire Size: **20 – 18 AWG**

Features

Product Type Features

Receptacle Style	180°
Sealable	No

Contact Features

Contact Size	.64mm
Contact Fabrication	Stamped & Formed
Wire Contact Termination Area Plating Material	Tin
Typical Current Rating	7.7 A
Crimp Type	F-Crimp
Terminal Type	Tab
Mating Tab Width	.8 mm[.031 in]
Mating Tab Thickness	.64 mm[.025 in]
Interface Plating	Tin (Sn)

Termination Features

Termination Method to Wire & Cable	Crimp
Product Terminates To	Wire

Dimensions

Compatible Insulation Diameter Range	1.2 – 1.9 mm[.047 – .074 in]
Wire Size	.5 – .8 mm²



Wire Size Search	18 AWG, 19 AWG, 20 AWG
------------------	------------------------

Usage Conditions

Insulation Option	Uninsulated
Operating Temperature (Max)	80 °C, 85 °C, 90 °C, 100 °C, 105 °C, 110 °C, 120 °C, 125 °C[176 °F][185 °F][194 °F][212 °F][221 °F][230 °F][248 °F][257 °F]
Operating Temperature Range	-40 – 125 °C[-40 – 257 °F]

Operation/Application

Compatible With Wire Base Material	Copper
------------------------------------	--------

Packaging Features

Packaging Quantity	7000
Packaging Method	Package

Other

Terminal Transmits	0 – 24 A (Low Power)
--------------------	----------------------

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2023 (235) Candidate List Declared Against: JUNE 2023 (235) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not reviewed for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides



on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

 TE Part # 2151580-1 OCEAN_2.0_APPLICATOR-S-062F067F	 TE Part # 2151580-2 OCEAN_2.0_APPLICATOR-S-062F067FA	 TE Part # 2305570-1 Strip Terminal Cutter-Side Feed-No Crimp	 TE Part # 7-2151580-1 OCEAN_2.0_APPLICATOR-S-062F067F
 TE Part # 7-2151580-2 OCEAN_2.0_APPLICATOR-S-062F067FA	 TE Part # 7-2151580-7 OCEAN_2.0_SPARE_PART_KIT-062F067F	 TE Part # 638379-3 .64MM 2X4 CAP ASSY, KEY C	 TE Part # 1438726-2 70 Way Inline Sealed Hybrid Cap Assy

Also in the Series | AMP 0.64 Connector System

 Automotive Connector Caps & Covers (17)	 Automotive Housings(25)	 Automotive Terminals(14)	 Insertion & Extraction Tools(1)
 Other Automotive Connector Accessories(2)	 PCB Headers & Receptacles(30)		


Customers Also Bought



TE Part #1-331366-0
PIDG SPDFLG 22-16COM22-18MIL10




TE Part #1326132-1
18WAY LAC SHIELD ASSEMBLY 70 D



TE Part #967056-1
MQS BLINDSTOPFEN4MM




TE Part #828904-2
SINGLE WIRE SEAL FOR J.P.T.CON



TE Part #175567-1
HYBRID I/O CONN PLUG HSG 26P




TE Part #1318670-2
025 TPS CONN PLUG HSG ASSY 3P




TE Part #1393366-1
V23540X7000Y 21=GET-FEM TERM S



TE Part #638551-1
CONTACT,FEMALE,0.64MM,SN,18-20



TE Part #8-1437188-8
FST-23A-25V3



TE Part #1456315-1
SLECTIVE PLUG SOCKET ASY SIEM

Documents

Product Drawings

MALE TERM. 18-20AWG, SN, RE-RE

English

MALE TERM. 18-20AWG, SN, RE-RE

English

CAD Files

Customer View Model

ENG_CVM_1488220-1_O1.3d_igs.zip

English

Customer View Model

ENG_CVM_1488220-1_O1.3d_stp.zip

English

Customer View Model

ENG_CVM_1488220-1_O1.2d_dxf.zip

English

3D PDF

English

By downloading the CAD file I accept and agree to the Terms and Conditions of use.



Product Specifications

Application Specification

English

Instruction Sheets

Instruction Sheet (U.S.)

English

Instruction Sheet (U.S.)

English