



Terminals & Splices > Splices > CoolSplice Quick Connect Splice



Wire Size: .34 – .52 mm²

Sealable: No

Splice Capacity: 4

Splice Features: End Feed

[All CoolSplice Quick Connect Splice \(12\)](#)

Features

Product Type Features

Sealable	No
Splice Type	Butt Splice
Compatible With Discrete Wire Type	Solid, Stranded
Wire Insulation Support Retention Type	Insulation Support

Configuration Features

Splice Capacity	4
Compatible With Wire & Cable Type	Discrete Wire

Electrical Characteristics

Current Rating	5 A
Operating Voltage	600 V

Body Features

Button Color	Green
Splice Features	End Feed



Contact Features

Contact Base Material	Phosphor Bronze
-----------------------	-----------------

Mechanical Attachment

Wire Insulation Support	With
-------------------------	------

Dimensions

Wire Size	.34 – .52 mm²
Compatible Insulation Diameter Range	2.85 mm[.112 in]
Product Length	36.4 mm[1.433 in]

Usage Conditions

Insulation Option	Fully Insulated
Operating Temperature Range	-40 – 105 °C[-40 – 221 °F]

Operation/Application

Compatible With Wire Base Material	Copper
------------------------------------	--------

Industry Standards

Compatible With Agency/Standards Products	IEC, UL
Compatible With Approved Standards Products	IEC 60988-2-3, UL 1977, UL 2459
UL Flammability Rating	UL 94V-2
Government Qualified Splice	No

Packaging Features

Packaging Method	Box
------------------	-----

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2023 (235) Candidate List Declared Against: JUNE 2023 (235) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free



Solder Process Capability

Not reviewed for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

TE Part # 2213800-4
COOLSPICE NEW STANDARD

Also in the Series | CoolSplice Connectors

Splices(12)

Customers Also Bought


TE Part #7-1625966-3
HSA10 56R 5%

TE Part #735410
ELECTRO TAP ASSY


TE Part #2106124-2
Contact, Tab, Tin Plated, Std Lgth

TE Part #794762-1
12P UMNLCAP HSG WHITE,PAN MNT







TE Part #794276-1
06P UMNL WIRE SEAL




TE Part #454100-000
D-406-0002




TE Part #967398-000
D-406-0001



TE Part #280708-2
MOD 2 CONTACT



TE Part #794270-1
02P UMNL WIRE SEAL



TE Part #7-2836878-7
OC-055F060O-CRIMPTOOLINGKIT

Documents

Product Drawings

COOLSPLICE NEW STANDARD

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_2213800-3_D2.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_2213800-3_D2.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_2213800-3_D2.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

CoolSplice New Standard flyer (Chinese)

English

CoolSplice Connector

CoolSplice Connector

English

Product Specifications

Application Specification



English

Instruction Sheets

Instruction Sheet (U.S.)

English

Agency Approvals

DEKRA_CB_NL-68996_C1 CoolSplice IEC60998-2-3

English