

1986775-4

✓ ACTIVE

Buchanan

TE Internal #: 1986775-4


PCB Terminal Blocks, Header, Wire-to-Component, 4 Position, .2 in

[5.08 mm] Centerline, 2 Row, 90° Wire Entry Angle, 20 – 1 AWG

Wire Size

[View on TE.com >](#)

Connectors > Terminal Blocks & Strips > PCB Terminal Blocks

Terminal Block Connector Type: **Header**Connector System: **Wire-to-Component**Number of Positions: **4**Centerline (Pitch): **5.08 mm [.2 in]**Number of Rows: **2**

Features

Product Type Features

Wire Protection	With
Terminal Block Connector Type	Header
Connector System	Wire-to-Component
Connector & Contact Terminates To	Printed Circuit Board

Configuration Features

Wire Entry Location	Side
Stacking Configuration	Side Stackable
Number of Positions	4
Number of Rows	2
Wire Entry Angle	90°

Electrical Characteristics

Operating Voltage	300 VAC
-------------------	---------

Body Features

Primary Product Color	Green
-----------------------	-------

Product Orientation

Contact Features

Contact Mating Area Plating Material	Tin
Contact Base Material	Copper Alloy
Contact Current Rating (Max)	15 A

Termination Features

Termination Post & Tail Length	3.5 mm [.138 in]
Termination Method to Printed Circuit Board	Through Hole - Solder
Termination Method to Wire & Cable	Push-in, Spring Terminal

Mechanical Attachment

Connector Mounting Type Board Mount

Housing Features

Housing Material	PA 66
Centerline (Pitch)	5.08 mm[.2 in]

Dimensions

Wire Size .5 – 41 mm²

Usage Conditions

Operating Temperature Range -40 – 110 °C[-40 – 230 °F]

Operation/Application

Circuit Application Power & Signal

Product Compliance

For compliance documentation, visit the product page on TE.com

EU RoHS Directive 2011/65/EU	Compliant with Exemptions
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	<p>Current ECHA Candidate List: JUNE 2023 (235)</p> <p>Candidate List Declared Against: JUNE 2023 (235)</p> <p>SVHC > Threshold: Pb (.63% in Component Part)</p> <p>Article Safe Usage Statements: Do not eat, drink or smoke when using this product. Wash thoroughly after handling. Recycle if possible and dispose of the article by following all applicable governmental regulations relevant to your geographic location.</p>

Halogen Content

Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free


Solder Process Capability

Not reviewed for solder process capability


Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 1986712-4
SCREWLESS, SW,4P,5.08 PCB




TE Part # 1986816-4
PCB SPRNG SIDE ENTRY HITEMP TB
5.08MM 4P


Customers Also Bought



TE Part #2-6609115-3
6EGG1-2=F7386D



TE Part #5499923-3
A/L UNIV HDR 16P VERT LG LAT



TE Part #5748026-1
15 PLUG SP/FMS (IN,SL)



TE Part #34072
SPLICE,PG BUTT 12-10



TE Part #1986712-3
SCREWLESS, SW,3P,5.08 PCB



TE Part #5-1618241-6
K81C235=RELAY, VACUUM, SPDT



TE Part #4-1419108-0
RTE24005F



TE Part #382811-6
SHUNT, ECON, PHBR 15 AU, BLACK



TE Part #2176238-7
CPF A 0805 22R 0.1% 25PPM 5K RL

Documents

Product Drawings

[SCREWLESS, SW,4P,5.08 PCB, Low Amp](#)

English

CAD Files

[3D PDF](#)

3D

Customer View Model

[ENG_CVM_CVM_1986775-4_B.2d_dxf.zip](#)

English

Customer View Model

[ENG_CVM_CVM_1986775-4_B.3d_jgs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_1986775-4_B.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

[BUCHANAN TERMINAL BLOCKS CATALOG - EUROSTYLE TERMINAL BLOCKS](#)

English

Agency Approvals

[UL](#)

English