



Terminals & Splices > Terminal Housings, Insulation Sleeves & Blocks > Cluster Blocks



Number of Circuits: 3

Primary Product Material: PBT

Wire Size: .3 – 2 mm²

Operating Temperature Range: -20 – 120 °C [-4 – 248 °F]

Features

Product Type Features

Compatible With Discrete Wire Type	Lead Wire
------------------------------------	-----------

Configuration Features

Number of Circuits	3
--------------------	---

Body Features

Primary Product Color	Natural
Primary Product Material	PBT

Contact Features

Mating Pin Diameter	2.29 mm[.09 in]
---------------------	-----------------

Mechanical Attachment

Block Mounting Configuration	1 Forward - 2 Back
Mount Diameter	13.46 mm[.53 in]

Dimensions

Product Length	31.49 mm[1.239 in]
Wire Size	.3 – 2 mm ²

Usage Conditions

--	--



Operating Temperature Range	-20 – 120 °C[-4 – 248 °F]
-----------------------------	---------------------------

Industry Standards

UL Flammability Rating	UL 94HB
------------------------	---------

Packaging Features

Packaging Quantity	1
Packaging Method	Package

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2023 (235) Candidate List Declared Against: JUNE 2023 (235) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 3-2005820-9
CLUSTER BLOCK 3P SLIM HSG(GWT)

TE Part # 1217264-1
RCPT 090 CLSTR PIN 22-14

TE Part # 62131-3
CLSTR PIN RCPT

TE Part # 1742964-1
2.29 DIA CLUSTER PIN AMPLV REC 1600-4800

TE Part # 1217172-1
Cluster Block Rcpt Amplivar 400-1600

TE Part # 1742981-1
2.29 DIA CLUST PIN AMPLVR REC 400-1600

TE Part # 2825468-1
CLSTR PIN RCPT 0.5SQMM

Customers Also Bought

TE Part #3-2176055-2
RLP73K 2B R20 1% 1K RL

TE Part #1-215919-0
AMP-LATCH 15.2 HIGH TAPE

TE Part #928205-2
2P TELFIX BU-GEH

TE Part #280050-7
250 FASTON, FLAG, REC., 16-20 AWG, TPPB

TE Part #60733-1
PIN .090 RECEPTACLE TPPHBZ

TE Part #1-2176397-5
3502 3R9 1%

TE Part #160739-2
250 FASTON, PIGGYBACK REC., 18-14 AWG, TPBR

TE Part #6-1393239-5
RT234012

TE Part #165565-2
2,8 PIDG FASTON REC

TE Part #2-2176397-0
3502 6R2 1%

Documents



Product Drawings

090 DIA CLSTR BLK

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_360050-1_AF_c-360050-1-af.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_360050-1_AF_c-360050-1-af.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_360050-1_AF_c-360050-1-af.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

Magnet Wire Terminals & Splices

English

Product Specifications

Engineering Report

English

Agency Approvals

Agency Approval Document

English