




Terminals & Splices > Automotive Terminals > Contacts: Size 16, 13A



Terminal Type: Pin

Mating Pin Diameter: 1.59 mm [.063 in]

Terminal Transmits: 0 – 24 A (Low Power)

Wire Size: .82 – 1.31 mm²

[All Contacts: Size 16, 13A \(33\)](#)

Features

Product Type Features

Receptacle Style	180°
Sealable	No
Primary Locking Feature	Clean Body

Contact Features

Contact Size	Size 16
Contact Fabrication	Stamped & Formed
Wire Contact Termination Area Plating Material	Tin
Typical Current Rating	13 A
Crimp Type	F-Crimp
Terminal Type	Pin
Mating Pin Diameter	1.59 mm[.063 in]
Interface Plating	Nickel (Ni)

Termination Features





Termination Method to Wire & Cable	Crimp
Product Terminates To	Wire

Dimensions

Wire Size	.82 – 1.31 mm²
Wire Size Search	16 AWG, 17 AWG, 18 AWG

Usage Conditions

Insulation Option	Uninsulated
Operating Temperature (Max)	80 °C, 85 °C, 90 °C, 100 °C, 105 °C, 110 °C, 120 °C[176 °F][185 °F][194 °F][212 °F][221 °F][230 °F][248 °F]
Operating Temperature Range	-40 – 120 °C[-40 – 248 °F]

Operation/Application

Compatible With Wire Base Material	Copper
------------------------------------	--------

Packaging Features

Packaging Quantity	4000
Packaging Method	Reel

Other

Terminal Transmits	0 – 24 A (Low Power)
--------------------	----------------------

Product Compliance

For compliance documentation, visit the product page on TE.com>





EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2023 (235) Candidate List Declared Against: JUNE 2023 (235) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer



This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>


Compatible Parts

 TE Part # CAT-AM7801-CH8172 AMPSEAL 16 Housings	 TE Part # 2151617-1 OCEAN-2.0-APPLICATOR-S-090F1300	 TE Part # 2151617-2 OCEAN-2.0-APPLICATOR-S-090F1300A	 TE Part # 2305570-1 Strip Terminal Cutter-Side Feed-No Crimp
 TE Part # 2320926-1 2POS,AMPSEAL 16,PIN HSG ASSY, SLD,COD 1	 TE Part # 2320926-2 2POS,AMPSEAL 16,PIN HSG ASSY, SLD,COD 2	 TE Part # 2320926-3 2POS,AMPSEAL 16,PIN HSG ASSY, SLD,COD 3	 TE Part # 2320926-4 2POS,AMPSEAL 16,PIN HSG ASSY, SLD,COD 4
 TE Part # 7-2151617-1 OCEAN-2.0-APPLICATOR-S-090F1300	 TE Part # 7-2151617-2 OCEAN-2.0-APPLICATOR-S-090F1300A	 TE Part # 7-2151617-7 OCEAN_2.0_SPARE_PART_KIT-090F1300	

Also in the Series | AMPSEAL 16



Automotive Connector Caps & Covers
(1)



Automotive Connector Locks & Position Assurance(2)



Automotive Housings(244)



Automotive Terminals(33)



Connector Backshells(84)



Connector Seals & Cavity Plugs(4)



Data Connectivity Headers(2)



Data Connectivity Housings(3)



Other Automotive Connector Accessories(11)

Customers Also Bought




TE Part #1-2035366-0
AMPSEAL 16 Connectors Backshell



TE Part #2040594-5
SEAL CAP HSG 8P, AMPSEAL16 SEA



TE Part #776492-2
Contacts: Size 16, 13A



TE Part #776363-1
SEALING PLUG, SZ 16 CAVITY



TE Part #C34252-000
ES1000-NO.3-B8-X-55MM



TE Part #0830956003
RBK-85-NR5100/A-X-12MM

Documents



Product Drawings

PIN, SF, SIZE 16, 16-18 AWG, NI/SN

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_2098250-3_A.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_2098250-3_A.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_2098250-3_A.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

ICT Terminals and Connectors Catalogue

English

CONNECTOR SELECTOR

English

Product Specifications

Product Specification

English