




Connectors > Terminal Blocks & Strips > PCB Terminal Blocks



Terminal Block Connector Type: **Header**

Connector System: **Wire-to-Board**

Number of Positions: **5**

Centerline (Pitch): **5.08 mm [.2 in]**

Number of Rows: **2**

Features

Product Type Features

Header Type	Fully Shrouded
Terminal Block Connector Type	Header
Connector System	Wire-to-Board
Connector & Contact Terminates To	Printed Circuit Board

Configuration Features

Stacking Configuration	Side Stackable
Number of Positions	5
Number of Rows	2

Electrical Characteristics

Operating Voltage	300 VAC
-------------------	---------

Body Features

Primary Product Color	Green
Product Orientation	Right Angle



Contact Features

Contact Mating Area Plating Material	Tin
Contact Base Material	Copper Alloy
Contact Current Rating (Max)	15 A

Termination Features

Termination Post & Tail Length	3.5 mm[.138 in]
Termination Method to Printed Circuit Board	Through Hole - Solder
Termination Method to Wire & Cable	Push-in

Mechanical Attachment

Connector Mounting Type	Board Mount
-------------------------	-------------

Housing Features

Housing Material	PA 66
Centerline (Pitch)	5.08 mm[.2 in]

Dimensions

Wire Size	.05 – 3 mm²
-----------	-------------

Usage Conditions

Operating Temperature Range	-40 – 105 °C[-40 – 221 °F]
-----------------------------	----------------------------

Operation/Application

Circuit Application	Power & Signal
---------------------	----------------

Packaging Features

Packaging Quantity	150
Packaging Method	Box

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant with Exemptions
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2023 (235) Candidate List Declared Against: JUNE 2023 (235) Does not contain REACH SVHC



Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Wave solder capable to 240°C

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

TE Part # 796634-5 5 POS 5.08MM R/A PLUG,TRM BLK	TE Part # 284041-5 TERMINAL BLOCK VERTICAL PLUG S	TE Part # 284047-5 TERMI-BLOK VERTICAL PLUG STACK	TE Part # 1776166-5 5P TERMI-BLOK HDR,HIGH TEMP
TE Part # 1776167-5 5P TERMI-BLOK HDR,HIGH TEMP	TE Part # 1986262-5 Female Spring Connector, Green, 5.08, 10	TE Part # 282807-5 3P TERMI-BLOK PLUG,MARKED	

Customers Also Bought

TE Part #5227222-3 VERT JK W/MTG PINS, BNC PCB	TE Part #776230-1 35POS,PIN DIA 1.3,HDR ASSY, 180DEG,COD 1	TE Part #1-2176070-8 3521 51R 1% 2W	TE Part #5556591-1 MJ,LPF,R/A,8P/8C,SHLD,KEYEDP



TE Part #3-1825059-0
ADFO6STTR04=DIP S,FLUSH,SMT-GW

TE Part #1734366-1
Std USB Type A, VT, T/H

TE Part #6-104071-0
08 SYSTEM 50 HDR SRST SHRD SN

TE Part #641976-1
15P UMNL PIN HDR ASSY POL 94VO

TE Part #3-215297-6
36P HV100 REC CON. TE, 7.0MM

Documents

Product Drawings

TERMI-BLOK HDR 90, 5,08MM P. M

English

CAD Files

Customer View Model

ENG_CVM_284061-5_B.3d_igs.zip

English

Customer View Model

ENG_CVM_284061-5_B.3d_stp.zip

English

Customer View Model

ENG_CVM_284061-5_B.2d_dxf.zip

English

3D PDF

English

3D PDF

3D

Customer View Model

ENG_CVM_CVM_284061-5_D.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_284061-5_D.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_284061-5_D.3d_stp.zip

English



By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

Eurostyle Terminal Blocks Focus Product Stock List

English

BUCHANAN TERMINAL BLOCKS CATALOG - EUROSTYLE TERMINAL BLOCKS

English

1-1773458-1_EURO_STYLE_TERMINAL_BLOCKS_QRG

English

Product Specifications

Application Specification

English

Agency Approvals

UL

English