

2-1415068-1

✓ ACTIVE

SCHRACK | SCHRACK Slimline PCB Relay SNR

TE Internal #: 2-1415068-1

Power Relays, Standard, Monostable, DC, 170 mW Coil Power
 Rating DC, 848 Ω Coil Resistance, UL Coil Insulation Class F,
 SCHRACK Slimline PCB Relay SNR

[View on TE.com >](#)

Relays & Contactors > Relays > Power Relays

Power Relay Type: **Standard**Coil Magnetic System: **Monostable, DC**Coil Power Rating DC: **170 mW**Coil Resistance: **848 Ω**Coil Special Features: **UL Coil Insulation Class F**

Features

Product Type Features

Power Relay Type	Standard
------------------	----------

Electrical Characteristics

Insulation Initial Dielectric Between Coil & Contact Class	3500 – 4000 V
Insulation Initial Dielectric Between Contacts & Coil	1000 V
Contact Limiting Making Current	10 A
Contact Limiting Short-Time Current	6 A
Contact Limiting Continuous Current	10 A
Insulation Creepage Class	5.5 – 8 mm
Coil Power Rating Class	150 – 200 mW
Insulation Creepage Between Contact & Coil	8 mm[.315 in]
Contact Limiting Breaking Current	6 A
Coil Magnetic System	Monostable, DC
Coil Power Rating DC	170 mW
Coil Resistance	848 Ω
Coil Special Features	UL Coil Insulation Class F
Coil Voltage Rating	12 VDC
Contact Switching Load (Min)	100mA @ 12V
Contact Switching Voltage (Max)	400 VAC

Contact Voltage Rating

250 VAC

Body Features

Insulation Special Features

Tracking Index of Relay Base PTI250

Product Weight

6 g [.2116 oz]

Contact Features

Contact Arrangement

1 Form A (NO)

Contact Current Class

16 A

Contact Current Rating (Max)

6 A

Contact Material

AgNi90/10

Contact Number of Poles

1

Relay Terminal Type

PCB-THT

Mechanical Attachment

Relay Mounting Type

Printed Circuit Board

Dimensions

Length Class (Mechanical)

25 – 30 mm

Width Class (Mechanical)

0 – 6 mm

Product Width

5 mm [.197 in]

Product Length

28 mm

Usage Conditions

Environmental Ambient Temperature Class

70 – 85 °C

Environmental Ambient Temperature (Max)

85 °C [185 °F]

Packaging Features

Packaging Method

Box & Tube, Tube

Product ComplianceFor compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU

Compliant

EU ELV Directive 2000/53/EC

Compliant

China RoHS 2 Directive MIIT Order No 32, 2016

No Restricted Materials Above Threshold

EU REACH Regulation (EC) No. 1907/2006

Current ECHA Candidate List: JUNE 2023 (235)

Candidate List Declared Against: JUNE 2023 (235)

Does not contain REACH SVHC

Halogen Content

Not Low Halogen - contains Br or Cl > 900 ppm.

Solder Process Capability

Wave solder capable to 260°C

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts




TE Part # 1415068-1
V23092-A1005-A802



TE Part # 5-1416250-0
V23092B1005A802




TE Part # 2-1416100-0
ST3FLC4

Also in the Series | [SCHRACK Slimline PCB Relay SNR](#)

Power Relays(53)

Customers Also Bought



Documents

CAD Files

[3D PDF](#)

3D

Customer View Model

[ENG_CVM_CVM_2-1415068-1_C.2d_dxf.zip](#)

English

Customer View Model

[ENG_CVM_CVM_2-1415068-1_C.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_2-1415068-1_C.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

[Slim PCB Relay SNR](#)

English

Product Specifications

Definitions General Purpose Relays

English

Agency Approvals

[VDE Certificate](#)

English