




- 1.CIRCUIT:ON/OFF
- 2.PCB CONNECTOR TYPE; SINGLE POLE SINGLE THROW)
- 3.RATING: 6A GP 125/250VAC(UL;CUL)
6(1)A 250V~ T125/55(ENEC17;NEMKO)
- 4.CONTACT RESISTANT: <50mΩ (INITIAL)
- 5.INSULATION RESISTANCE: >100MΩ
(500VDC BETWEEN OPEN CONTACTS)
- 6.DIELECTRIC STRENGTH: 1500V 1MIN
- 7.MECHANICAL LIFE: >30000 CYCLES
- 8.ELECTRICAL LIFE: >10000 CYCLES
- 9.TEMPERATURE RISE AT THE TERMINAL: MAX. 30°C
- 10.SOLDER ABILITY OF TERMINAL: MAX350°C, 3S
(NO PRESSURE MAY BE
PLACED IN THE TERMINALS WHEN SOLDERING BY HAND)
- 11.ACTUATOR & HOUSING COLOR: BLACK
- 12.ACTUATOR PRINTING COLOR: WHITE
- 13.ALL MATERIALS ARE ROHS COMPLIANT
- 14.OPERATION FORCE:250±100gf



HOUSING TYPE:PC IN PANEL



5	→	10	→	DIMENSIONAL TOLERANCES		APPROVED	CHECKED	DESIGN	DRAWN	ALL SIZE ARE IN	MM		
4	→	9	→	RANGE	TOLERANCE				LMC 2019. 12. 10	SCALE	NO		
3	→	8	→	X	±0.30					MAT'L	***		
2	→	7	→	X.X	±0.20					MATERIAL NO.		DRAWING NO.	REV.
1	增加UL安规 2020. 08. 19	6	→	X.XX	±0.10	LEGION ELECTRONIC & HARDWARE CO., LTD.					SS01-BBIWL-RB20-R	WIF119160	A1
NO	DESCRIPTION	NO	DESCRIPTION	ANGLES	±1°								