



- 1.电路CIRCUIT:ON/OFF
2.快插端子 QUICK CONNECTOR TYPE;
单刀单掷 (SINGLE POLE SINGLE THROW);
3.额定值RATING:16A 125/250VAC (UL;C-UL);
12A 125/250VAC (UL;C-UL);
16(4)A 250V~T125/55(ENEC17;NEMKO;CQC;CB)





UL APPROVAL FILE NO.:E153399
ENEC CERTIFICATE NO.:NO3715
NEMKO CERTIFICATE NO.:P09211556/A1
CQC CERTIFICATE NO.10002049681
CB CERTIFICATE NO.:NO62986/A2


- 4.柄的颜色ACTUATOR COLOR: 白色WHITE
基座的颜色 HOUSING COLOR: 白色WHITE
5.柄的印字形式ACTUATOR PRINTING:"  " 白色WHITE COLOR
6.所有部件均使用环保材料
ALL MATERIALS USE IN CONFORMIY WITH THE RoHS DIRECTIVE

TEL : 0769-82310511-867



PANEL CUTOUT DIMENSION,PANEL THICKNESS 0.8~1.2mm



5	→	10	→	DIMENSIONAL TOLERANCES		APPROVED	CHECKED	DESIGN	DRAWN	ALL SIZE ARE IN	MM		
4	→	9	→	RANGE	TOLERANCE				LMC	SCALE	NO		
3	→	8	→	X	±0.30				2019.05.20	MAT'L	***		
2	→	7	→	X.X	±0.20					MATERIAL NO.		DRAWING NO.	REV.
1	→	6	→	X.XX	±0.10							SS11-WWIBQ-RR20-R	*****
NO	DESCRIPTION	NO	DESCRIPTION	ANGLES	±1°	LEGION ELECTRONIC & HARDWARE CO., LTD.							A0