




Connectors > Contacts > Connector Contacts



Contact Type: **Pin**

Contact Mating Area Plating Material: **Tin**

Wire Contact Termination Area Plating Material: **Pre-Tin**

Operating Voltage: **600 VAC**

Contact Retention Within Housing: **With**

Features

Electrical Characteristics

Operating Voltage	600 VAC
-------------------	---------

Contact Features

Mating Square Post Dimension	1.14 mm[.045 in]
Wire Contact Termination Area Plating Thickness	2.54 µm[100 µin]
Wire Contact Termination Area Plating Material Finish	Bright
Contact Mating Area Plating Material Thickness	2.54 µm[100 µin]
Contact Orientation	Straight
Contact Type	Pin
Contact Mating Area Plating Material	Tin
Wire Contact Termination Area Plating Material	Pre-Tin
Contact Retention Within Housing	With
Contact Base Material	Brass
Contact Current Rating (Max)	9 A

Termination Features



Termination Method to Wire & Cable	Crimp
Product Terminates To	Wire & Cable

Mechanical Attachment

Wire Insulation Support	Without
-------------------------	---------

Dimensions

Compatible Insulation Diameter Range	1.5 – 3.1 mm [.06 – .122 in]
Wire Size	.33 – .82 mm²

Usage Conditions

Operating Temperature Range	-40 – 105 °C [-40 – 221 °F]
-----------------------------	-----------------------------

Operation/Application

Circuit Application	Power
---------------------	-------

Packaging Features

Packaging Quantity	3500
Packaging Method	Reel

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2023 (235) Candidate List Declared Against: JUNE 2023 (235) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not reviewed for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits



as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

TE Part # 2825212-1 VAL-U-LOK PIN HCS TN 22-18 LP	TE Part # 2825213-1 VAL-U-LOK SKT HCS SN 22-18 LP	TE Part # 2151096-1 OCEAN-2.0-APPLICATOR-S-062F125F	TE Part # 2238020-1 VAL-U-LOK PIN BR TN 22-18 LP
TE Part # 2238021-1 VAL-U-LOK SKT BR SN 22-18 LP	TE Part # 2151096-2 OCEAN-2.0-APPLICATOR-S-062F125FA	TE Part # 2305570-1 Strip Terminal Cutter-Side Feed-No Crimp	TE Part # 5-2151096-1 OCEAN-2.0-APPLICATOR-S-062F125F
TE Part # 5-2151096-2 OCEAN-2.0-APPLICATOR-S-062F125FA	TE Part # 7-2151096-1 OCEAN-2.0-APPLICATOR-S-062F125F	TE Part # 7-2151096-2 OCEAN-2.0-APPLICATOR-S-062F125FA	TE Part # 7-2151096-7 OCEAN_2.0_SPARE_PART_KIT-062F125F
TE Part # 7-2836879-7 OC-062F125F-752-CRIMP TOOLING KIT			


Customers Also Bought



TE Part #1-770849-5
15P SL156 HSG W/LOC RAMP W/TBS




TE Part #521282-2
ULTRA-POD 250 ASSY REC 18-14 AWG TPBR



TE Part #1969614-6
6P RCPT VAL-U-LOK V0



TE Part #1969608-3
3P VAL-U-LOK TPA 22-18 AWG




TE Part #794956-5
VAL-U-LOK SKT BR SN 18-22AWG



TE Part #293041-2
FF 250 TAB 0.35-1.0MM2 TPBR



TE Part #42800-1
187 FASTON REC 20-16 AWG BR



TE Part #2238019-1
VAL-U-LOK SKT BR SN 22-26AWG



TE Part #794760-1
06P UMNL CAP HSG WHITE,PAN MNT



TE Part #1-1969612-0
10P FH PLUG VAL-U-LOK V0

Documents

Product Drawings

VAL-U-LOK PIN BR SN 18-22AWG

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_2238016-1_A_c-2238016-1-a.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_2238016-1_A_c-2238016-1-a.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_2238016-1_A_c-2238016-1-a.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages



1-1773730-3 VAL-U-LOK Connectors with TPA Flyer

English

Product Specifications

Application Specification

English

Instruction Sheets

Instruction Sheet (U.S.)

English