## Product data sheet Characteristics

## RPM21FD

Harmony, Power plug-in relay, 15 A, 2 CO, with lockable test button, 110 V DC



#### Main Range of Product Harmony Electromechanical Relays Series name Power **Product or Component** Plug-in relay Type Device short name RPM Contacts type and 2 C/O composition [Uc] control circuit 110 V DC voltage [Ithe] conventional 15 A -40...131 °F (-40...55 °C) enclosed thermal current Status LED Without Control Type Lockable test button

20 %

#### Complementary

Flat
250 V IEC
300 V CSA 300 V UL
4 kV 1.2/50 μs
AgNi
15 A 277 V AC) UL
15 A 28 V DC) UL 15 A 250 V AC) NO IEC
15 A 28 V DC) NO IEC
7.5 A 250 V AC) NC IEC
7.5 A 28 V DC) NC IEC
250 V IEC
15 A 250 V AC
15 A 28 V DC
3750 VA
420 W
170 mW 10 mA, 17 V
<= 1200 cycles/hour under load
<= 18000 cycles/hour no-load
10000000 cycles
100000 cycles resistive
0.85 W
>= 0.1 Uc DC
20 ms at nominal voltage
20 ms at nominal voltage
13440 Ohm at 68 °F (20 °C) +/- 10 %
88121 V DC
RTI
Level A
Any position
3
B10d = 100000
0.08 lb(US) (0.036 kg)
Complete product

Utilisation coefficient

### Environment

Dielectric strength	1500 V AC between contacts with micro disconnection 2000 V AC between coil and contact with reinforced 2000 V AC between poles with basic	
Standards	UL 508 EN/IEC 61810-1 CSA C22.2 No 14	
Product Certifications	CSA UL EAC	
Ambient Air Temperature for Storage	-40185 °F (-4085 °C)	
Ambient air temperature for operation	-40131 °F (-4055 °C)	
Vibration resistance	3 gn +/- 1 mm 10150 Hz)5 cycles in operation 5 gn +/- 1 mm 10150 Hz)5 cycles not operating	
Degree of protection (Housing only)	IP40 conforming to EN/IEC 60529	
Shock resistance	15 gnin operation 30 gnnot operating	

### Ordering and shipping details

ordoring and ompping dotailo	
Category	21127 - ZELIO ICE CUBE RELAYS
Discount Schedule	CP2
GTIN	3389119401852
Nbr. of units in pkg.	1
Package weight(Lbs)	1.31 oz (37 g)
Returnability	No
Country of origin	CN

## Packing Units

Unit Type of Package 1	PCE
Package 1 Height	1.85 in (4.7 cm)
Package 1 width	0.83 in (2.1 cm)
Package 1 Length	1.10 in (2.8 cm)
Unit Type of Package 2	BB1
Number of Units in Package 2	10
Package 2 Weight	14.07 oz (399 g)
Package 2 Height	1.22 in (3.1 cm)
Package 2 width	4.13 in (10.5 cm)
Package 2 Length	4.92 in (12.5 cm)
Unit Type of Package 3	S01
Number of Units in Package 3	120
Package 3 Weight	11.24 lb(US) (5.1 kg)
Package 3 Height	5.91 in (15 cm)
Package 3 width	5.91 in (15 cm)
Package 3 Length	15.75 in (40 cm)

## Offer Sustainability


California proposition 65	WARNING: This product can expose you to chemicals including: Nickel compounds, which is known to the State of California to cause cancer, and Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
REACh Regulation	REACh Declaration
REACh free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EEU RoHS  Declaration
Toxic heavy metal free	Yes
Mercury free	Yes

RoHS exemption information	<b>⊡</b> Yes
China RoHS Regulation	China RoHS Declaration
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.
Contractual warranty	
Warranty	18 months


# Product data sheet Dimensions Drawings

## RPM21FD

### **Dimensions**




Pin Side View



## Wiring Diagram






Symbols shown in blue correspond to Nema marking.

#### **Electrical Durability of Contacts**

Durability (inductive load) = durability (resistive load) x reduction coefficient.


Resistive AC load



X Switching capacity (kVA)


Y Durability (Number of operating cycles)

Reduction coefficient for inductive AC load (depending on power factor cos φ)



Y Reduction coefficient (A)

Maximum switching capacity on resistive DC load



X Voltage DC

Y Current DC

Note: These are typical curves, actual durability depends on load, environment, duty cycle, etc.