


[Relays & Contactors > Relays > Power Relays > STD OEG Miniature PCB OJ/OJE Pow Relays](#)Power Relay Type: **Standard**Coil Magnetic System: **Monostable, DC**Coil Power Rating DC: **200 mW**Coil Resistance: **720 Ω** Coil Special Features: **UL Coil Insulation Class F**[All STD OEG Miniature PCB OJ/OJE Pow Relays \(65\)](#)

Features

Product Type Features

Power Relay Type	Standard
------------------	----------

Electrical Characteristics

Insulation Initial Dielectric Between Coil & Contact Class	2500 – 3000 V
Insulation Initial Dielectric Between Open Contacts	750 Vrms
Contact Limiting Making Current	8 A
Contact Limiting Short-Time Current	8 A
Contact Limiting Continuous Current	8 A
Insulation Creepage Class	3 – 5.5 mm
Coil Power Rating Class	150 – 200 mW
Insulation Initial Dielectric Between Contacts & Coil	3000 Vrms
Insulation Creepage Between Contact & Coil	3.6 mm [.141 in]
Contact Limiting Breaking Current	8 A
Coil Magnetic System	Monostable, DC

Coil Power Rating DC	200 mW
Coil Resistance	720 Ω
Coil Special Features	UL Coil Insulation Class F
Coil Voltage Rating	12 VDC
Contact Switching Load (Min)	100mA @ 5V
Contact Switching Voltage (Max)	30 VDC
Contact Voltage Rating	30 VDC

Body Features

Insulation Special Features	Tracking Index of Relay Base PTI250
Product Weight	9 g [.318 oz]

Contact Features

Contact Arrangement	1 Form A (NO)
Contact Current Class	16 A
Contact Current Rating (Max)	8 A
Contact Material	AgCdO
Contact Number of Poles	1
Relay Terminal Type	PCB-THT

Mechanical Attachment

Relay Mounting Type	Printed Circuit Board
---------------------	-----------------------

Dimensions

Length Class (Mechanical)	16 – 20 mm
Insulation Clearance Class	0 – 2.5 mm
Height Class (Mechanical)	14 – 15 mm
Insulation Clearance Between Contact & Coil	3.2 mm [.126 in]
Width Class (Mechanical)	10 – 12 mm
Product Width	10.2 mm [.4 in]
Product Length	18.2 mm [.717 in]
Product Height	14.7 mm [.579 in]

Usage Conditions

Environmental Ambient Temperature Class	50 – 70 °C
Environmental Ambient Temperature (Max)	70 °C [158 °F]

Packaging Features

Packaging Method

Box & Tray, Tray

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU

Compliant with Exemptions

EU ELV Directive 2000/53/EC

Compliant

China RoHS 2 Directive MIIT Order No 32, 2016

Restricted Materials Above Threshold

EU REACH Regulation (EC) No. 1907/2006

Current ECHA Candidate List: JUNE 2023
(235)Candidate List Declared Against: JUNE
2023 (235)

SVHC > Threshold:

Cadmium oxide (4.75% in Component Part)

Article Safe Usage Statements:

Use personal protective equipment as required. Do not eat, drink or smoke when using this product. Recycle if possible and dispose of the article by following all applicable governmental regulations relevant to your geographic location.

Halogen Content

Not Low Halogen - contains Br or Cl > 900
ppm.


Solder Process Capability

Wave solder capable to 265°C

Product Compliance Disclaimer


This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts




TE Part # CAT-OE4-OJ1
STD OEG Miniature PCB OJ/OJE Pow
Relays

Also in the Series | [OEG Miniature PCB Relay OJ/OJE](#)



Power Relays(67)

Customers Also Bought

TE Part #3-640443-5
05P MTA100 CONN ASSY GRNTE Part #1-2232890-3
3P MONOPLUG 2.5 SELECTIVELY LOADEDTE Part #521781-1
250 HSG. PL MKIII REC. 6.81mm 4P NATTE Part #175150-2
AMP UNIVE. POWER CONN TAB CONTTE Part #1742543-1
250 FASTON,FLAG,REC.,18-12 AWG, NPSTTE Part #1461400-5
OJE-SH-112LMHF,000TE Part #1649222-1
OJE-SS-112DM,801TE Part #2366410-1
187 PL MII REC. 22-18AWG PTBRTE Part #2366413-1
187 PL MII REC. 18-16AWG PTBRTE Part #62131-9
CLSTR PIN RCPT

Documents

Product Drawings

OJE-SH-112LMHF,000

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_1721870-5_E.2d_dxf.zip

English

Customer View Model

[ENG_CVM_CVM_1721870-5_E.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_1721870-5_E.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

[OJ_OJE Series Relay Data Sheet English](#)

English

Product Specifications

[PCH TRAY PACKING](#)

English

[Definitions General Purpose Relays](#)

English

Agency Approvals

[VDE Certificate](#)

English