

ANT-1.4-CW-HWR-SMA

✓ ACTIVE

TE Internal #: L9000011-01

Terminal/Duck Antenna, Single Band, Cellular, External Mount, Connector, SMA, Omnidirectional, Single Port, Gain 0 < 3 dBi

[View on TE.com >](#)



Antennas



Wireless Application: **Cellular**

Mounting Location: **External**

Mounting Type: **Connector**

Antenna Termination: **SMA**

Antenna Type: **Terminal/Duck**

Features

Product Type Features

Antenna Product Type	Antenna
Antenna Termination	SMA

Configuration Features

Antenna Style	Whip
Mounting Location	External
Antenna Type	Terminal/Duck
Band Type	Single Band
Port Configuration	Single Port

Electrical Characteristics

VSWR (Max)	<2.1:1
Impedance	50 Ω

Signal Characteristics

Gain (Max)	2.4 dB
Frequency Band	1400 MHz
Nominal Frequency Range	1164 – 1610
Peak Gain	0 < 3 dBi

Body Features

Product Weight	13.24 g[.46701 oz]
----------------	--------------------



Mechanical Attachment

Polarization	Linear
Mounting Type	Connector

Dimensions

Product Width	10 mm[.39 in]
Product Length	142 mm[5.59 in]
Product Height	0 mm[0 in]

Operation/Application

Antenna Environment	Outdoor
Directionality	Omnidirectional

Industry Standards

Wireless Application	Cellular
Primary Application	Cellular

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant with Exemptions
EU ELV Directive 2000/53/EC	Not Yet Reviewed
China RoHS 2 Directive MIIT Order No 32, 2016	Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2023 (235) Not Yet Reviewed
Halogen Content	Not Yet Reviewed for halogen content
Solder Process Capability	Not reviewed for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulations, TE’s information on SVHC in articles for this part number is still based on the European Chemical Agency (ECHA) ‘Guidance on requirements for substances in articles’(Version: 2, April 2011), applying the 0.1% weight on weight concentration threshold at the finished product level. TE is aware of the European Court of Justice ruling of September 10th, 2015 also known as O5A (Once An Article Always An Article) stating that, in case of ‘complex object’, the threshold for a SVHC must be applied to both the













product as a whole and simultaneously to each of the articles forming part of its composition. TE has evaluated this ruling based on the new ECHA “Guidance on requirements for substances in articles” (June 2017, version 4.0) and will be updating its statements accordingly.

Compatible Parts

 <p>TE Part # CONSMA001 SMA Jack 50 Ohm PCB Through Hole</p>	 <p>TE Part # CONSMA002-L-G SMA Jack 50 Ohm PCB Through Hole</p>	 <p>TE Part # CONSMA002-SMD-G SMA Jack 50 Ohm PCB Surface Mount</p>	 <p>TE Part # CONSMA008-G SMA Jack 50 Ohm Through Hole PCB</p>
---------------------------------------------------------------------------------------------------------------------------------------------------	-------------------------------------------------------------------------------------------------------------------------------------------------------	------------------------------------------------------------------------------------------------------------------------------------------------------------	-------------------------------------------------------------------------------------------------------------------------------------------------------

Customers Also Bought

 <p>TE Part #327639 SPLICE BUTT PIDG 12-10/22-18</p>	 <p>TE Part #1676625-3 HSA25 270R 5%</p>	 <p>TE Part #894153-000 22759/32-12-2</p>	 <p>TE Part #2-323916-1 TERMINAL,PIDG R 26-22 8</p>
 <p>TE Part #YDTS20W09-98PNV001 RECP ASSY</p>	 <p>TE Part #1757824-7 AMPLIMITE,ASY,RCPT,STD,90,ZN,1,CT</p>	 <p>TE Part #751023-000 55A1121-12-9/96-9CS2275</p>	 <p>TE Part #216365-001 22759/32-14-9</p>
 <p>TE Part #L9000020-01 Antenna 1/2 Wave Whip Swivel 2.4 GHz SMA</p>	 <p>TE Part #MS27488-12-2 SEALING PLUGS</p>		

Documents

Product Drawings
Antenna 1/2 Wave Whip Swivel 1.4GHz SMA
English



Datasheets & Catalog Pages

Sub-6 Cellular LTE-5G NR Frequency Band Guide

English

Virtual Antenna

English

Microsplatch Ground Plane Optimization

English

ANT-1.4-CW-HWR-ccc

English

VHETH Antenna Series Ground Plane Optimization

English

Considerations for Operation within the 260-470MHz Band

English

Understanding Antenna Specifications and Operation

English

Antennas Design, Application and Performance

English

The FCC Road Part 15 From Concept to Approval

English

RF 101 Information for the RF Challenged

English