




Connectors > PCB Connectors > PCB Headers & Receptacles



PCB Connector Assembly Type: **PCB Mount Receptacle**

PCB Mount Orientation: **Vertical**

Connector System: **Board-to-Board**

Number of Positions: **5**

Number of Rows: **2**

Features

Product Type Features

PCB Connector Assembly Type	PCB Mount Receptacle
Connector System	Board-to-Board
Sealable	No
Connector & Contact Terminates To	Printed Circuit Board

Configuration Features

Stackable	Yes
PCB Mount Orientation	Vertical
Number of Positions	5
Number of Rows	2

Body Features

Connector Profile	Standard
Primary Product Color	Black

Contact Features

Contact Protection Type	Closed Entry Housing
Mating Square Post Dimension	.63 mm[.024 in]
PCB Contact Termination Area Plating Material Thickness	2.5 µm[98.425 µin]
Mating Pin Diameter	.63 mm[.024 in]
Contact Shape & Form	Square



PCB Contact Termination Area Plating Material	Tin
Contact Base Material	Phosphor Bronze
Contact Mating Area Plating Material	Gold
	30 μin
Contact Type	Socket
Contact Current Rating (Max)	3 A

Termination Features

Rectangular Termination Post & Tail Thickness	.2 mm[.008 in]
Rectangular Termination Post & Tail Width	.69 mm[.027 in]
Termination Post & Tail Length	3.1 mm[.122 in]
Termination Method to Printed Circuit Board	Through Hole - Solder

Mechanical Attachment

PCB Mount Retention Type	Retention Solder Tails
PCB Mount Retention	With

Housing Features

Mating Entry Location	Top
Centerline (Pitch)	2.54 mm[.1 in]
Housing Material	Polyester - GF

Dimensions

Connector Height	7 mm[.276 in]
Row-to-Row Spacing	2.54 mm
PCB Thickness (Recommended)	1.6 mm

Usage Conditions

Operating Temperature Range	-65 – 125 °C, -55 – 105 °C
-----------------------------	----------------------------

Operation/Application

Solder Process Feature	Board Standoff
------------------------	----------------

Industry Standards

UL Flammability Rating	UL 94V-0
------------------------	----------

Packaging Features

Packaging Quantity	144
Packaging Type	Carton



Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2023 (235) Candidate List Declared Against: JUNE 2023 (235) Does not contain REACH SVHC
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Wave solder capable to 265°C


Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 1241050-5
2x5P MOD II BREAK AWAY HDR,SMD, BLISTER



TE Part # 826632-5
5P AMPMODU II PIN HDR



TE Part # 826656-5
5P AMPMODU II STIFT LEI



TE Part # 826634-5
05P MODU 2 PIN HDR.



TE Part # 826658-5
5P AMPMODU II STIFT LEI

TE Part # 826662-5
5P AMPMODU II STIFT LEI

TE Part # 966269-5
2x5P MOD II BREAK AWAY HDR,SMD, TUBE PKG

TE Part # 215447-5
2X 5P MOD2 STIFTLEI

TE Part # 826664-5
5P MOD2 STIFT LEI

TE Part # 828430-5
2X 5P AMPMODU II STIFTLEI

TE Part # 829394-5
2X5P MOD II UNSHRD HDR, ST, 0.8 AU

TE Part # 826659-5
MOD2 HEADER DR 5P

TE Part # 966709-5
2X5P MODU II BREAK AWAY HEADER, SMD

Also in the Series

AMPMODU HV-100/HV-190

PCB Headers & Receptacles(333)

Customers Also Bought

TE Part #215307-4
2X4P HV100 REC CON. TE, 7.0MM

TE Part #215297-5
5P HV100 REC CON. TE, 7.0MM

TE Part #8-1676481-0
CPF 0603 16K 0.1% 25PPM 1K RL

TE Part #3-2319764-1
E STACK PIANO 2P G LONG T&R PD ON



TE Part #6-1879417-8
CPF0603 604K 0.1% 25PPM 1K RL

TE Part #5-2176421-5
TLRP 2512 2.0W R025 1% 50PPM 4K RL

TE Part #9541-040C-S-C-3-T
PRESSURE I2C 0.6 PSIG SO16

TE Part #HPP845E031R1
I.C 21D RH/T B1500

Documents

Product Drawings
2X5P HV100 REC CON. TE, 7.0MM
English

CAD Files
3D PDF
3D
Customer View Model
ENG_CVM_CVM_215307-5_F.2d_dxf.zip
English
Customer View Model
ENG_CVM_CVM_215307-5_F.3d_igs.zip
English
Customer View Model
ENG_CVM_CVM_215307-5_F.3d_stp.zip
English

By downloading the CAD file I accept and agree to the Terms and Conditions of use.

Product Specifications
Connector System HV-100
German
Product Specification
German