



DEUTSCH

TE Internal #: 2-2600021-3
Automotive Terminals, Socket, Pin Diameter 1.56 mm [.061 in], 18 – 14 AWG Wire Size, .8 – 2 mm² Wire Size, Sealable, Family Seal

[View on TE.com >](#)

Terminals & Splices > Automotive Terminals



Terminal Type: **Socket**
Mating Pin Diameter: **1.56 mm [.061 in]**
Terminal Transmits: **0 – 24 A (Low Power)**
Wire Size: **.8 – 2 mm²**

Features

Product Type Features

| | |
|-------------------------|------------|
| Sealable | Yes |
| Primary Locking Feature | Clean Body |

Body Features

| | |
|--------------------|-------------|
| Terminal Seal Type | Family Seal |
|--------------------|-------------|

Contact Features

| | |
|------------------------|------------------|
| Contact Size | Size 16 |
| Contact Fabrication | Stamped & Formed |
| Typical Current Rating | 10 A |
| Crimp Type | F-Crimp |
| Terminal Type | Socket |
| Mating Pin Diameter | 1.56 mm[.061 in] |
| Interface Plating | Nickel (Ni) |

Termination Features

| | |
|------------------------------------|-------|
| Termination Method to Wire & Cable | Crimp |
| Product Terminates To | Wire |



Dimensions

| | |
|------------------|--|
| Wire Size | .8 – 2 mm ² |
| Wire Size Search | 14 AWG, 15 AWG, 16 AWG, 17 AWG, 18 AWG |
| Tab Length | 9.2 mm[.362 in] |

Usage Conditions

| | |
|-----------------------------|---|
| Insulation Option | Uninsulated |
| Operating Temperature (Max) | 80 °C, 85 °C, 90 °C, 100 °C, 105 °C, 110 °C, 120 °C, 125 °C[176 °F][185 °F][194 °F][212 °F][221 °F][230 °F][248 °F][257 °F] |
| Operating Temperature Range | -55 – 125 °C[-67 – 257 °F] |

Operation/Application

| | |
|------------------------------------|--------|
| Compatible With Wire Base Material | Copper |
|------------------------------------|--------|

Packaging Features

| | |
|--------------------|------|
| Packaging Quantity | 3000 |
| Packaging Method | Reel |

Other

| | |
|--------------------|----------------------|
| Terminal Transmits | 0 – 24 A (Low Power) |
|--------------------|----------------------|

Product Compliance

For compliance documentation, visit the product page on TE.com>

| | |
|---|---|
| EU RoHS Directive 2011/65/EU | Compliant |
| EU ELV Directive 2000/53/EC | Compliant |
| China RoHS 2 Directive MIIT Order No 32, 2016 | No Restricted Materials Above Threshold |
| EU REACH Regulation (EC) No. 1907/2006 | Current ECHA Candidate List: JUNE 2023 (235) Candidate List Declared Against: JUNE 2023 (235) Does not contain REACH SVHC |
| Halogen Content | Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free |
| Solder Process Capability | Not reviewed for solder process capability |

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as



EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

TE Part # 2837880-1
OCEAN-2.0-APPLICATOR-S-102F1100

TE Part # 2837880-2
OCEAN-2.0-APPLICATOR-S-102F1100

TE Part # 7-2837880-1
OCEAN-2.0-APPLICATOR-S-102F1100

TE Part # 7-2837880-2
OCEAN-2.0-APPLICATOR-S-102F1100

TE Part # 7-2837880-7
OCEAN_2.0_SPARE_PART_KIT-102F1100

TE Part # 2-2600020-2
XRC PIN TERMINAL 14-18AWG Ni Plated

Customers Also Bought

TE Part #HDP26-24-23SN-L017
DEUTSCH HDP20 Housings

TE Part #1-967587-3
6POS MQS TAB SEALED COD A

TE Part #953122-1
40W MQS COVER ASSY (15D)

TE Part #4-2600020-2
XRC PIN TERMINAL 16-20AWG Ni Plated

TE Part #5-2600021-3
XRC SOCKET 20-24 AWG Ni Plated

TE Part #1565804-2
025 G 8POS CAP ASSY W TO W

TE Part #2-964296-1
TAB A 2.8x0.8 CONTACT CF SRC Sn

TE Part #2600042-2
12CCT RECEP BLACK K A W/SMALL SEAL



Documents

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_2-2600021-3_1.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_2-2600021-3_1.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_2-2600021-3_1.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications

Application Specification

English