








SURFACES FLUSH ± 0.10



DETAIL 'B'
SCALE 20 : 1



RECOMMENDED PCB LAYOUT

Specifications

Frequency Range:DC0~3G

VSWR:1.3MAX

Working Voltage:500V rms @ sea level

Insulation Resistance:5000 Ohms min

Temperature Range:-55°C TO +155°C

Relative Temperature:≤95%(40° C±2° C)

Drawings products are in line with ROHS standards

NOTE:

DRAWN
Zelin. Zhang
2012/11/10


CHECKED

APPROVALS
John
12/04/2012

Tolerance

0-6 ± 0.15
6-30 ± 0.20
30-120 ± 0.5
Angular $\pm 2^\circ$

View



UNIT

MM

SCALE

1:1



Dosin Industrial(H.K)Co.Ltd

东莞市德索五金电子制品有限公司

Dosin Hardware Electronics Co.,Ltd

Name:

MMCX JACK CONNECTOR

SIZE
A

Product NO.

DOSIN-809-0029

REV
A

DateTime

2012/11/02

CAD FILE

D/company drawings/BD

SHEET: 1 OF 1

E-mail:dosin2005@163.com
dosin2005@dosing-china.com
Web:http://www.dosingconn.com
TEL:(0086)769-81153906
FAX:(0086)769-81875836